



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer David W	Contact Title	Product Compliance Engineer for DND																											
Company Unique ID	TE Connectivity	Response Date	2018-07-10	Contact Email	dave.benfer@te.com																													
Contact Phone Number		717-986-3725																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	2-1761606-3	Amount	2781.921448	Version	-	Identity																												
Manufacturer Item Name	IDC LOW PRO HDR 10P VERT LG LAT BLUE	Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH																																	
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	IDC BANDOLIER POST 30 DPLX				10.0	41.0921448	mg																										
Material	2	Tin Plate				10.0	0.21974	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	10.0	4.3948E-4	mg																										
Substance	3	Tin	Supplier	7440-31-5	99.73	10.0	0.21915	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	10.0	1.5382E-4	mg																										
Material	2	Gold Flash				10.0	0.0775387	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	10.0	2.3262E-4	mg																										
Substance	3	Gold	Supplier	7440-57-5	99.7	10.0	0.07730608	mg																										
Material	2	Nickel Plate				10.0	0.490712	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	10.0	9.8142E-4	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	10.0	4.9071E-4	mg																										
Substance	3	Nickel	Nickel	7440-02-0	99.7	10.0	0.48924	mg																										
Material	2	Gold Plate				10.0	0.0861541	mg																										
Substance	3	Gold	Supplier	7440-57-5	99.7	10.0	0.08589564	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	10.0	2.5846E-4	mg																										
Material	2	Phos Bronze				10.0	40.218	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	10.0	4.0218E-4	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.015	10.0	0.0060327	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.02	10.0	0.0080436	mg																										
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	10.0	0.14076	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	10.0	0.0040218	mg																										
Substance	3	Tin	Supplier	7440-31-5	5.8	10.0	2.33264	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	10.0	0.040218	mg																										

Substance	3	Zinc	Supplier	7440-66-6	0.3	10.0	0.12065	mg	
Substance	3	Copper	Supplier	7440-50-8	93.1335	10.0	37.45643	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	10.0	0.0040218	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	10.0	0.040218	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	10.0	0.040218	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	10.0	0.0040218	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	10.0	2.0109E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	10.0	0.020109	mg	
Sub-Item	1	1K02502="ES" 501 EJECTOR VERT				1.0	642.7	mg	
Material	2	Zinc Alloy				1.0	627.0	mg	
Substance	3	Iron	Supplier	7439-89-6	0.08	1.0	0.5016	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.0627	mg	
Substance	3	Zinc	Supplier	7440-66-6	95.1925	1.0	596.85697	mg	
Substance	3	Copper	Supplier	7440-50-8	0.25	1.0	1.5675	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.00627	mg	
Substance	3	Magnesium	Supplier	7439-95-4	0.02	1.0	0.1254	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.01	1.0	0.0627	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.0627	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.00627	mg	
Substance	3	Aluminum	Supplier	7429-90-5	4.3	1.0	26.961	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.627	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0030	1.0	0.01881	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0020	1.0	0.01254	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.003135	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.02	1.0	0.1254	mg	
Material	2	Copper Plate				1.0	13.0	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.013	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	12.987	mg	
Material	2	Nickel Plate				1.0	2.7	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.0054	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.0027	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	2.6919	mg	
Sub-Item	1	1K02504="ES" 501 EJECTOR VERT				1.0	641.5	mg	
Material	2	Zinc Alloy				1.0	626.0	mg	
Substance	3	Iron	Supplier	7439-89-6	0.08	1.0	0.5008	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.0626	mg	
Substance	3	Zinc	Supplier	7440-66-6	95.1925	1.0	595.90505	mg	
Substance	3	Copper	Supplier	7440-50-8	0.25	1.0	1.565	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.00626	mg	
Substance	3	Magnesium	Supplier	7439-95-4	0.02	1.0	0.1252	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.01	1.0	0.0626	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.0626	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.00626	mg	
Substance	3	Aluminum	Supplier	7429-90-5	4.3	1.0	26.918	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.626	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0030	1.0	0.01878	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0020	1.0	0.01252	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00313	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.02	1.0	0.1252	mg	
Material	2	Copper Plate				1.0	12.9	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.0129	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	12.8871	mg	
Material	2	Nickel Plate				1.0	2.6	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.0052	mg	

Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.0026	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	2.5922	mg	
Sub-Item	1	1K02403=BAS E 10 POS HEADER VER				1.0	1086.8	mg	
Material	2	PBT-GF30-FR(17)				1.0	1086.8	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	51.0	1.0	554.268	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	8.0	1.0	86.944	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	29.0	1.0	315.172	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	4.0	1.0	43.472	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	156042-31-8	8.0	1.0	86.944	mg	