



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	TE Product Compliance	Contact Title			
Company Unique ID	TE Connectivity	Response Date	2018-09-26	Contact Email	productcompliance@te.com				
Contact Phone Number	+001-800-522-6752								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5-1879215-5	Amount	5.4231E-4	Version	-	Identity			
Manufacturer Item Name	CPF 0402 16K5 0.1% 25PPM 1K RL	Weight Uom	g	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Material	1	Resistor Layer				1.0	1.0E-8	g	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	100.0	1.0	1.0E-8	g	
Material	1	Nickel Plating				1.0	1.447965E-6	g	
Substance	2	Nickel	Nickel	7440-02-0	100.0	1.0	1.447965E-6	g	
Material	1	Backside Electrode				1.0	6.23113E-6	g	
Substance	2	Terpineol	Supplier	8000-41-7	15.0	1.0	9.346696E-7	g	
Substance	2	Copper oxide (CuO)	Supplier	1317-38-0	10.0	1.0	6.23113E-7	g	
Substance	2	Ethanol, 2-(2-butoxyethoxy)-	Supplier	112-34-5	20.0	1.0	1.246226E-6	g	
Substance	2	Silver	Supplier	7440-22-4	55.0	1.0	3.427122E-6	g	
Material	1	Edge Electrode				1.0	1.0E-8	g	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	100.0	1.0	1.0E-8	g	
Material	1	Overcoat				1.0	4.98382E-6	g	
Substance	2	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	10.0	1.0	4.98382E-7	g	
Substance	2	Carbon black	Supplier	1333-86-4	3.0	1.0	1.495146E-7	g	
Substance	2	Resin acids and Rosin acids	Supplier	73138-82-6	35.0	1.0	1.744337E-6	g	
Substance	2	Silica, vitreous	Supplier	60676-86-0	20.0	1.0	9.967639E-7	g	
Substance	2	Acetamide	Supplier	60-35-5	20.0	1.0	9.967639E-7	g	
Substance	2	Ethanol, 2-(2-butoxyethoxy)-	Supplier	112-34-5	12.0	1.0	5.980584E-7	g	
Material	1	Tin Plating				1.0	3.416547E-6	g	
Substance	2	Tin	Supplier	7440-31-5	100.0	1.0	3.416547E-6	g	
Material	1	Substrate				1.0	5.1999E-4	g	
Substance	2	Magnesium oxide (MgO)	Supplier	1309-48-4	1.0	1.0	5.199893E-6	g	
Substance	2	Aluminum oxide (Al2O3)	Supplier	1344-28-1	96.0	1.0	4.9919E-4	g	

Substance	2	Quartz (SiO ₂)	Supplier	14808-60-7	3.0	1.0	1.559968E-5	g	
Material	1	Upside Electrode				1.0	6.23113E-6	g	
Substance	2	Ethanol, 2-(2-butoxyethoxy)-	Supplier	112-34-5	20.0	1.0	1.246226E-6	g	
Substance	2	Copper oxide (CuO)	Supplier	1317-38-0	10.0	1.0	6.23113E-7	g	
Substance	2	Silver	Supplier	7440-22-4	55.0	1.0	3.427122E-6	g	
Substance	2	Terpineol	Supplier	8000-41-7	15.0	1.0	9.346696E-7	g	