



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Wu, Cc	Contact Title	Engineer Product Compliance china																											
Company Unique ID	TE Connectivity	Response Date	2018-06-07	Contact Email	cc.wu@te.com																													
Contact Phone Number		86-2124071672																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	3-640620-3	Amount	559.606	Version	-	Identity																												
Manufacturer Item Name	03P MTA100 CONN ASSY F/T RED	Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed																																	
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	MTA100 CONT 22AWG SN / PHBZ				3.0	93.202	mg																										
Material	2	Phos Bronze				3.0	90.4	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.02	3.0	0.01808	mg																										
Substance	3	Copper	Supplier	7440-50-8	93.1485	3.0	84.20624	mg																										
Substance	3	Zinc	Supplier	7440-66-6	0.3	3.0	0.2712	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.01	3.0	0.00904	mg																										
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	3.0	0.3164	mg																										
Substance	3	Iron	Supplier	7439-89-6	0.1	3.0	0.0904	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	3.0	0.00452	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	3.0	9.04E-4	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	3.0	0.0904	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	3.0	0.00904	mg																										
Substance	3	Tin	Supplier	7440-31-5	5.8	3.0	5.2432	mg																										
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	3.0	0.00452	mg																										
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	3.0	4.52E-4	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	3.0	0.0452	mg																										
Substance	3	Nickel	Nickel	7440-02-0	0.1	3.0	0.0904	mg																										
Material	2	Tin Plate				3.0	2.221	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	3.0	0.004442	mg																										
Substance	3	Tin	Supplier	7440-31-5	99.73	3.0	2.215	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	3.0	0.0015547	mg																										
Material	2	Nickel Plate				3.0	0.581	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	3.0	0.001162	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	3.0	5.81E-4	mg																										
Substance	3	Nickel	Nickel	7440-02-0	99.7	3.0	0.57926	mg																										

Sub-Item	1	03P MTA100 HSG RED FT W/O TBS				1.0	280.0	mg	
Material	2	PA66				1.0	274.4	mg	
Substance	3	Poly[imino(1,6- dioxo-1,6- hexanediyl)imi no-1,6- hexanediyl]	Supplier	32131-17-2	99.355	1.0	272.63012	mg	
Substance	3	Zinc oxide (ZnO)	Supplier	1314-13-2	0.0020	1.0	0.005488	mg	
Substance	3	Octadecanami de, N,N-1,2- ethanediylbis-	Supplier	110-30-5	0.3	1.0	0.8232	mg	
Substance	3	Water	Supplier	7732-18-5	0.2	1.0	0.5488	mg	
Substance	3	Aluminum, hydroxybis(oct adecanoato- .kappa.O)-	Supplier	300-92-5	0.14	1.0	0.38416	mg	
Substance	3	Siloxanes and Silicones, di- Me	Supplier	63148-62-9	0.0030	1.0	0.008232	mg	
Material	2	COLORANT				1.0	5.6	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2- 1212	6.29	1.0	0.35224	mg	
Substance	3	Poly[imino(1- oxo-1,6- hexanediyl)]	Supplier	25038-54-4	93.71	1.0	5.24776	mg	