



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer, Eng Proc Opt/LEANPD		
Company Unique ID	TE Connectivity	Response Date	2017-03-04	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1-745492-8	Amount	5025.73704	Version	-	Identity			
Manufacturer Item Name	09 HDE MS PLUG,22-26,LEAD FREE	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0616	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	SUB ASSY,SZ 1,PLUG,LEAD FREE				1.0	4028.883	mg	
Material	2	Carbon Steel				1.0	1824.0	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.08	1.0	1.4592	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.02	1.0	0.3648	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.02	1.0	0.3648	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.1824	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.02	1.0	0.3648	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.15	1.0	2.736	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	1.824	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.1824	mg	
Substance	3	Molybdenum	Supplier	7439-98-7	0.75	1.0	13.68	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.4	1.0	7.296	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.1	1.0	1.824	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.01824	mg	
Substance	3	Iron	Supplier	7439-89-6	98.1785	1.0	1790.77584	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.912	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.1824	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00912	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	1.824	mg	
Material	2	Carbon Steel				1.0	786.0	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00393	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.0786	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.6	1.0	4.716	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.13	1.0	1.0218	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.04	1.0	0.3144	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.15	1.0	1.179	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.00786	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.02	1.0	0.1572	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.1	1.0	0.786	mg	

Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.786	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.0786	mg	
Substance	3	Iron	Supplier	7439-89-6	98.6835	1.0	775.65231	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.786	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.0393	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.393	mg	
Material	2	Tin Plate				1.0	57.384	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.11477	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	57.22906	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	0.0401688	mg	
Material	2	Copper Plate				1.0	57.499	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.057499	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	57.4415	mg	
Material	2	PBT-I-GF30-FR(17)				1.0	1304.0	mg	
Substance	3	Dolomite (CaMg(CO3)2)	Supplier	16389-88-1	0.5	1.0	6.52	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	35.0	1.0	456.4	mg	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	1.0	2.608	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.2	1.0	2.608	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	1.0	39.12	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	2.0	1.0	26.08	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	1.0	1.0	13.04	mg	
Substance	3	Chlorite-group minerals	Supplier	1318-59-8	0.5	1.0	6.52	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	13.04	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	36.6	1.0	477.264	mg	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	1.0	6.52	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	18.0	1.0	234.72	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	1.0	1.0	13.04	mg	
Substance	3	Quartz (SiO2)	Supplier	14808-60-7	0.5	1.0	6.52	mg	
Sub-Item	1	PIN, HDE, 22-26, LEAD FREE				9.0	110.76156	mg	
Material	2	Gold Plate				9.0	0.128985	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	9.0	0.1286	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	9.0	3.8695E-4	mg	
Material	2	Phos Bronze				9.0	106.0	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	9.0	100.38041	mg	

Substance	3	Manganese	Supplier	7439-96-5	0.02	9.0	0.0212	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	9.0	0.0106	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	9.0	4.77	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	9.0	0.0053	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	9.0	0.0106	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	9.0	0.106	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	9.0	0.00106	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	9.0	0.318	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	9.0	0.106	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	9.0	0.106	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	9.0	0.0053	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	9.0	0.053	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	9.0	0.106	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	9.0	5.3E-4	mg	
Material	2	Nickel Plate				9.0	2.485799	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	9.0	0.0049716	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	9.0	0.0024858	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	9.0	2.47834	mg	
Material	2	Tin Plate				9.0	2.146776	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	9.0	0.00429355	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	9.0	2.14098	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	9.0	0.00150274	mg	