



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	TE Product Compliance	<b>Contact Title</b>			
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2019-02-27	<b>Contact Email</b>	productcompliance@te.com				
<b>Contact Phone Number</b>	+001-800-522-6752								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	1-770174-1	<b>Amount</b>	1.370312	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	04P MINI UMNL ASSY VO SNAU LF	<b>Weight Uom</b>	g	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EURoHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-0117</b>	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
<b>Complex Article Description</b>	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	MINI UMNL BAND PIN SNAU LF				4.0	0.109843	g	
Material	2	Tin Plate				4.0	9.23E-4	g	
Substance	3	Tin	Supplier	7440-31-5	99.73	4.0	9.2051E-4	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	4.0	1.846E-6	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	4.0	6.461E-7	g	
Material	2	Gold Plate				4.0	2.73E-4	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	1.0	4.0	2.73E-6	g	
Substance	3	Gold	Supplier	7440-57-5	99.0	4.0	2.7027E-4	g	
Material	2	Nickel Plate				4.0	6.47E-4	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	4.0	1.294E-6	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	4.0	6.47E-7	g	
Substance	3	Nickel	Nickel	7440-02-0	99.7	4.0	6.4506E-4	g	
Material	2	Brass Wire				4.0	0.108	g	
Substance	3	Copper	Supplier	7440-50-8	71.5	4.0	0.07722	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	4.0	1.08E-6	g	
Substance	3	Zinc	Supplier	7440-66-6	28.0226	4.0	0.03026441	g	
Substance	3	Manganese	Supplier	7439-96-5	0.05	4.0	5.4E-5	g	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	4.0	1.08E-6	g	
Substance	3	Iron	Supplier	7439-89-6	0.05	4.0	5.4E-5	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	4.0	1.08E-4	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.0099	4.0	1.0692E-5	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	4.0	1.08E-5	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	4.0	5.4E-5	g	

Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	4.0	5.4E-6	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	4.0	5.4E-7	g	
Substance	3	Nickel	Nickel	7440-02-0	0.2	4.0	2.16E-4	g	
Sub-Item	1	04P MINI-UMNL HDR HSG V0 WHT				1.0	0.93094	g	
Material	2	PA66/6 FR(30)				1.0	0.0	g	
Substance	3	Nitrogen compounds - ISO 1043-4 code #FR(30)	Supplier	1043-4-FR30	10.0	1.0	0.0	g	
Substance	3	Polyamide Polymer Blend - ISO 1043-1 Term PA66+PA6	Supplier	1043-1-PA66+PA6	87.5	1.0	0.0	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0217	2.5	1.0	0.0	g	
Material	2	PA				1.0	0.93094	g	
Substance	3	Water	Supplier	7732-18-5	0.3262	1.0	0.00303673	g	
Substance	3	2H-Azepin-2-one, hexahydro-	Supplier	105-60-2	0.4637	1.0	0.00431677	g	
Substance	3	Siloxanes and Silicones, di-Me	Supplier	63148-62-9	3.0E-4	1.0	2.79282E-6	g	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediylo)imino-1,6-hexanediylo]	Supplier	32131-17-2	0.9451	1.0	0.00879831	g	
Substance	3	Benzenepropanamide, N,N-1,6-hexanediylobis[3,5-bis(1,1-dimethylethyl)-4-hydroxy-	Supplier	23128-74-7	0.4004	1.0	0.00372748	g	
Substance	3	1,2-Ethanediamine	Supplier	107-15-3	0.0033	1.0	3.072102E-5	g	
Substance	3	Phosphoric acid, sodium salt, hydrate (1:2:12)	Supplier	10039-32-4	0.025	1.0	2.3274E-4	g	
Substance	3	Octadecanoic acid, calcium salt (2:1)	Supplier	1592-23-0	0.2012	1.0	0.00187305	g	
Substance	3	Octadecanamide, N,N-1,2-ethanediylobis-	Supplier	110-30-5	0.1901	1.0	0.00176972	g	
Substance	3	1,3,5-Triazine-2,4,6-(1H,3H,5H)-trione, compd. with 1,3,5-triazine-2,4,6-triamine (1:1)	Supplier	37640-57-6	9.0717	1.0	0.08445208	g	
Substance	3	Hexanedioic acid, polymer with hexahydro-2H-azepin-2-one and 1,6-hexanediamine	Supplier	24993-04-2	88.373	1.0	0.82269961	g	