



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer David W	Contact Title	Product Compliance Engineer for DND		
Company Unique ID	TE Connectivity	Response Date	2018-06-20	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5103311-6	Amount	3496.87965906	Version	-	Identity			
Manufacturer Item Name	A/L LOW PRO HDR 26P RA BLACK	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	BAND ASSY .0245 SQ POST .805 30 AU				13.0	61.75250431	mg	
Material	2	Tin Plate				13.0	0.246	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	13.0	4.92E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	13.0	0.24534	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	13.0	1.722E-4	mg	
Material	2	Gold Flash				13.0	0.00807431	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	13.0	2.422293E-5	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	13.0	0.00805009	mg	
Material	2	Nickel Plate				13.0	0.747	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	13.0	0.001494	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	13.0	7.47E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	13.0	0.74476	mg	
Material	2	Gold Plate				13.0	0.05143	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	13.0	0.05127571	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	13.0	1.5429E-4	mg	
Material	2	Brass Wire				13.0	60.7	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	13.0	43.4005	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	13.0	6.07E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0226	13.0	17.00972	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	13.0	0.03035	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	13.0	6.07E-4	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	13.0	0.03035	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	13.0	0.0607	mg	

Substance	3	Arsenic	Supplier	7440-38-2	0.0099	13.0	0.0060093	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	13.0	0.00607	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	13.0	0.03035	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	13.0	0.003035	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	13.0	3.035E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	13.0	0.1214	mg	
Sub-Item	1	026 HOUSING LOPRO HDR				1.0	2082.4	mg	
Material	2	PA66-GF25				1.0	2082.4	mg	
Substance	3	Benzenamine, reaction products with aniline hydrochloride and nitrobenzene	Supplier	101357-15-7	4.0	1.0	83.296	mg	
Substance	3	Poly[[imino(1,6-dioxo-1,6-hexanediy)]imino-1,6-hexanediy]]	Supplier	32131-17-2	61.5	1.0	1280.676	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0217	3.5	1.0	72.884	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	6.0	1.0	124.944	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	520.6	mg	
Sub-Item	1	BAND ASSY .0245 SQ POST .606 30 AU				13.0	47.05362331	mg	
Material	2	Tin Plate				13.0	0.246189	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	13.0	4.9238E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	13.0	0.24552	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	13.0	1.7233E-4	mg	
Material	2	Gold Flash				13.0	0.00807431	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	13.0	2.422293E-5	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	13.0	0.00805009	mg	
Material	2	Nickel Plate				13.0	0.74793	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	13.0	0.00149586	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	13.0	7.4793E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	13.0	0.74569	mg	
Material	2	Gold Plate				13.0	0.05143	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	13.0	0.05127571	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	13.0	1.5429E-4	mg	
Material	2	Brass Wire				13.0	46.0	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	13.0	32.89	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	13.0	4.6E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0226	13.0	12.8904	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	13.0	0.023	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	13.0	4.6E-4	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	13.0	0.023	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	13.0	0.046	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0099	13.0	0.004554	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	13.0	0.0046	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	13.0	0.023	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	13.0	0.0023	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	13.0	2.3E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	13.0	0.092	mg	