



| | | | | | | | | | |
|---|---|--|---------------------------|----------------------|--------------------------------|----------------------|-------------------------------------|----------------------|------------------|
| Form Type | Distribute | Version | 2.0 | Ref | IPC 1752A | Sectionals | Material Info | Subsectionals | D, A |
| Supplier Information | | | | | | | | | |
| Company Name | TE Connectivity | Request Document ID | | Contact Name | Benfer David W | Contact Title | Product Compliance Engineer for DND | | |
| Company Unique ID | TE Connectivity | Response Date | 2018-07-11 | Contact Email | dave.benfer@te.com | | | | |
| Contact Phone Number | 717-986-3725 | | | | | | | | |
| Legal Statement | | | | | | | | | |
| Supplier Acceptance | true | | | | | | | | |
| Legal Statement | | | | | | | | | |
| The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers. | | | | | | | | | |
| Product | | | | | | | | | |
| Manufacturer Item number | 2040002-1 | Amount | 245.98 | Version | - | Identity | | | |
| Manufacturer Item Name | Micro USB REC type B DIP 4 legs assy(Au) | Weight Uom | mg | Mfr Site | | Authority | | | |
| Date | | UOM | Each | | | | | | |
| EUroHS-0508 | Product(s) meets EU RoHS requirement without any exemptions | | | | | | | | |
| ChinaRoHS-0508 | Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products | | | | | | | | |
| EUREACH-0117 | REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed | | | | | | | | |
| Complex Article Description | REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed | | | | | | | | |
| Product Disclosure | | | | | | | | | |
| Sub-Item/Material/Substance | Level | Name | Substance Category | Substance CAS | Substance Concentration | Quantity | Mass per Unit | UOM | Exemption |
| Sub-Item | 1 | Micro USB REC DIP 4legs SHELL type B(PL) | | | | 1.0 | 203.98 | mg | |
| Material | 2 | Tin Plate | | | | 1.0 | 1.88 | mg | |
| Substance | 3 | Contains No Reportable TE5081-2 Substances | Supplier | TE5081-2-1212 | 0.2 | 1.0 | 0.00376 | mg | |
| Substance | 3 | Tin | Supplier | 7440-31-5 | 99.73 | 1.0 | 1.87492 | mg | |
| Substance | 3 | Lead | Lead/Lead Compounds | 7439-92-1 | 0.07 | 1.0 | 0.001316 | mg | |
| Material | 2 | Stainless Steel | | | | 1.0 | 199.13 | mg | |
| Substance | 3 | Chromium | Supplier | 7440-47-3 | 18.0 | 1.0 | 35.8434 | mg | |
| Substance | 3 | Cobalt | Supplier | 7440-48-4 | 0.5 | 1.0 | 0.99565 | mg | |
| Substance | 3 | Phosphorus | Supplier | 7723-14-0 | 0.045 | 1.0 | 0.0896085 | mg | |
| Substance | 3 | Antimony | Supplier | 7440-36-0 | 0.01 | 1.0 | 0.019913 | mg | |
| Substance | 3 | Carbon | Supplier | 7440-44-0 | 0.15 | 1.0 | 0.2987 | mg | |
| Substance | 3 | Beryllium | Supplier | 7440-41-7 | 0.01 | 1.0 | 0.019913 | mg | |
| Substance | 3 | Silicon | Supplier | 7440-21-3 | 1.5 | 1.0 | 2.98695 | mg | |
| Substance | 3 | Manganese | Supplier | 7439-96-5 | 2.0 | 1.0 | 3.9826 | mg | |
| Substance | 3 | Arsenic | Supplier | 7440-38-2 | 0.03 | 1.0 | 0.059739 | mg | |
| Substance | 3 | Sulfur | Supplier | 7704-34-9 | 0.03 | 1.0 | 0.059739 | mg | |
| Substance | 3 | Iron | Supplier | 7439-89-6 | 68.6147 | 1.0 | 136.63245 | mg | |
| Substance | 3 | Lead | Lead/Lead Compounds | 7439-92-1 | 0.0999 | 1.0 | 0.19893 | mg | |
| Substance | 3 | Cadmium | Cadmium/Cadmium Compounds | 7440-43-9 | 0.0099 | 1.0 | 0.01971387 | mg | |
| Substance | 3 | Nickel | Nickel | 7440-02-0 | 9.0 | 1.0 | 17.9217 | mg | |
| Substance | 3 | Mercury | Mercury/Mercury Compounds | 7439-97-6 | 5.0E-4 | 1.0 | 9.9565E-4 | mg | |
| Material | 2 | Nickel Plate | | | | 1.0 | 2.97 | mg | |
| Substance | 3 | Contains No Reportable TE5081-2 Substances | Supplier | TE5081-2-1212 | 0.2 | 1.0 | 0.00594 | mg | |
| Substance | 3 | Lead | Lead/Lead Compounds | 7439-92-1 | 0.1 | 1.0 | 0.00297 | mg | |

| | | | | | | | | | |
|-----------|---|--|---------------------------|---------------|---------|-----|----------|----|--|
| Substance | 3 | Nickel | Nickel | 7440-02-0 | 99.7 | 1.0 | 2.96109 | mg | |
| Sub-Item | 1 | REC INSERT MOLD (Au&BLACK) MICRO USB | | | | 1.0 | 42.0 | mg | |
| Material | 2 | LCP-(GF+MD)40 | | | | 1.0 | 29.0 | mg | |
| Substance | 3 | Contains No Reportable TE5081-2 Substances | Supplier | TE5081-2-1212 | 2.0 | 1.0 | 0.58 | mg | |
| Substance | 3 | Glass, oxide, chemicals | Supplier | 65997-17-3 | 26.5 | 1.0 | 7.685 | mg | |
| Substance | 3 | Talc (Mg3H2(SiO3)4) | Supplier | 14807-96-6 | 12.7 | 1.0 | 3.683 | mg | |
| Substance | 3 | Carbon black | Supplier | 1333-86-4 | 1.0 | 1.0 | 0.29 | mg | |
| Substance | 3 | 1,3-Benzenedicarboxylic acid, polymer with 1,4-benzenedicarboxylic acid, [1,1-biphenyl]-4,4-diol and 4-hydroxybenzoic acid | Supplier | 60088-52-0 | 57.8 | 1.0 | 16.762 | mg | |
| Material | 2 | Nickel Plate | | | | 1.0 | 0.63 | mg | |
| Substance | 3 | Lead | Lead/Lead Compounds | 7439-92-1 | 0.1 | 1.0 | 6.3E-4 | mg | |
| Substance | 3 | Contains No Reportable TE5081-2 Substances | Supplier | TE5081-2-1212 | 0.2 | 1.0 | 0.00126 | mg | |
| Substance | 3 | Nickel | Nickel | 7440-02-0 | 99.7 | 1.0 | 0.62811 | mg | |
| Material | 2 | Gold Plate | | | | 1.0 | 0.25 | mg | |
| Substance | 3 | Gold | Supplier | 7440-57-5 | 99.7 | 1.0 | 0.24925 | mg | |
| Substance | 3 | Contains No Reportable TE5081-2 Substances | Supplier | TE5081-2-1212 | 0.3 | 1.0 | 7.5E-4 | mg | |
| Material | 2 | Phos Bronze | | | | 1.0 | 12.12 | mg | |
| Substance | 3 | Copper | Supplier | 7440-50-8 | 94.6985 | 1.0 | 11.47746 | mg | |
| Substance | 3 | Manganese | Supplier | 7439-96-5 | 0.02 | 1.0 | 0.002424 | mg | |
| Substance | 3 | Chromium | Supplier | 7440-47-3 | 0.01 | 1.0 | 0.001212 | mg | |
| Substance | 3 | Tin | Supplier | 7440-31-5 | 4.5 | 1.0 | 0.5454 | mg | |
| Substance | 3 | Arsenic | Supplier | 7440-38-2 | 0.0050 | 1.0 | 6.06E-4 | mg | |
| Substance | 3 | Iron | Supplier | 7439-89-6 | 0.1 | 1.0 | 0.01212 | mg | |
| Substance | 3 | Antimony | Supplier | 7440-36-0 | 0.01 | 1.0 | 0.001212 | mg | |
| Substance | 3 | Beryllium | Supplier | 7440-41-7 | 0.0010 | 1.0 | 1.212E-4 | mg | |
| Substance | 3 | Zinc | Supplier | 7440-66-6 | 0.3 | 1.0 | 0.03636 | mg | |
| Substance | 3 | Phosphorus | Supplier | 7723-14-0 | 0.1 | 1.0 | 0.01212 | mg | |
| Substance | 3 | Cobalt | Supplier | 7440-48-4 | 0.1 | 1.0 | 0.01212 | mg | |
| Substance | 3 | Cadmium | Cadmium/Cadmium Compounds | 7440-43-9 | 0.0050 | 1.0 | 6.06E-4 | mg | |
| Substance | 3 | Lead | Lead/Lead Compounds | 7439-92-1 | 0.05 | 1.0 | 0.00606 | mg | |
| Substance | 3 | Nickel | Nickel | 7440-02-0 | 0.1 | 1.0 | 0.01212 | mg | |
| Substance | 3 | Mercury | Mercury/Mercury Compounds | 7439-97-6 | 5.0E-4 | 1.0 | 6.06E-5 | mg | |