



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	TE Product Compliance	<b>Contact Title</b>			
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2018-12-07	<b>Contact Email</b>	productcompliance@te.com				
<b>Contact Phone Number</b>	+001-800-522-6752								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	1-1571983-0	<b>Amount</b>	0.696	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	GDH08S04=DIP SWITCH	<b>Weight Uom</b>	g	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-0117</b>	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
<b>Complex Article Description</b>	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Material	1	M plate_Au plating				1.0	4.0E-4	g	
Substance	2	Gold	Supplier	7440-57-5	100.0	1.0	4.0E-4	g	
Material	1	F plate				1.0	0.2882	g	
Substance	2	Phosphorus	Supplier	7723-14-0	0.25	1.0	7.205E-4	g	
Substance	2	Tin	Supplier	7440-31-5	8.0	1.0	0.023056	g	
Substance	2	Copper	Supplier	7440-50-8	91.3071428571429	1.0	0.26314719	g	
Substance	2	Zinc	Supplier	7440-66-6	0.178571428571429	1.0	5.1464E-4	g	
Substance	2	Iron	Supplier	7439-89-6	0.0857142857142857	1.0	2.4703E-4	g	
Substance	2	Nickel	Nickel	7440-02-0	0.178571428571429	1.0	5.1464E-4	g	
Material	1	M plate_Ni plating				1.0	4.0E-4	g	
Substance	2	Nickel	Nickel	7440-02-0	100.0	1.0	4.0E-4	g	
Material	1	F plate_Ni plating				1.0	0.0014	g	
Substance	2	Nickel	Nickel	7440-02-0	100.0	1.0	0.0014	g	
Material	1	F plate_Au plating				1.0	0.0014	g	
Substance	2	Gold	Supplier	7440-57-5	100.0	1.0	0.0014	g	
Material	1	M plate				1.0	0.0712	g	
Substance	2	Titanium	Supplier	7440-32-6	2.0	1.0	0.001424	g	
Substance	2	Copper	Supplier	7440-50-8	98.0	1.0	0.069776	g	
Material	1	COVER				1.0	0.037	g	
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	0.0111	g	
Substance	2	Benzene, 1,4-dichloro-, polymer with sodium sulfide (Na2S)	Supplier	26125-40-6	70.0	1.0	0.0259	g	
Material	1	Knod (Actuator)				1.0	0.016	g	

Substance	2	1,4-Benzenedicarboxylic acid, polymer with 1,2-ethanediol and 4-hydroxybenzoic acid	Supplier	25822-54-2	70.0	1.0	0.0112	g	
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	0.0048	g	
Material	1	Case				1.0	0.28	g	
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	0.084	g	
Substance	2	Benzene, 1,4-dichloro-, polymer with sodium sulfide (Na <sub>2</sub> S)	Supplier	26125-40-6	70.0	1.0	0.196	g	