



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Penica, John R	<b>Contact Title</b>	Sr Mgr Engineering, IND Central Eng		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2017-11-29	<b>Contact Email</b>	jrpenica@te.com				
<b>Contact Phone Number</b>	+1-717-592-3266								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	104652-3	<b>Amount</b>	0.45823728	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	30 50/50 GRID DRST SFMNT RCPT	<b>Weight Uom</b>	g	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EURoHS-0508</b>	Product(s) does not meet EU RoHS requirements and is not under exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is NOT eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-0117</b>	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
<b>Complex Article Description</b>	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	50/50 GRID RCPT CONT PLTD				30.0	0.0045	g	
Material	2	Gold Plate				30.0	5.179E-5	g	
Substance	3	Gold	Supplier	7440-57-5	99.7	30.0	5.163463E-5	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	30.0	1.5537E-7	g	
Material	2	Nickel Plate				30.0	2.36E-4	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	30.0	4.72E-7	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	30.0	2.36E-7	g	
Substance	3	Nickel	Nickel	7440-02-0	99.7	30.0	2.3529E-4	g	
Material	2	Tin-Lead Plate				30.0	7.3E-5	g	
Substance	3	Tin	Supplier	7440-31-5	86.5	30.0	6.3145E-5	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.5	30.0	3.65E-7	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	13.0	30.0	9.49E-6	g	
Material	2	Copper Alloy				30.0	0.00413921	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	30.0	2.069605E-6	g	
Substance	3	Zinc	Supplier	7440-66-6	1.0	30.0	4.13921E-5	g	
Substance	3	Silicon	Supplier	7440-21-3	1.2	30.0	4.967052E-5	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	30.0	4.13921E-6	g	
Substance	3	Copper	Supplier	7440-50-8	92.7685	30.0	0.00383988	g	
Substance	3	Chromium	Supplier	7440-47-3	0.06	30.0	2.483526E-6	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	30.0	4.13921E-8	g	
Substance	3	Magnesium	Supplier	7439-95-4	0.3	30.0	1.241763E-5	g	
Substance	3	Manganese	Supplier	7439-96-5	0.1	30.0	4.13921E-6	g	
Substance	3	Iron	Supplier	7439-89-6	0.2	30.0	8.27842E-6	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	30.0	2.069605E-7	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	30.0	4.13921E-7	g	

Substance	3	Nickel	Nickel	7440-02-0	4.2	30.0	1.7385E-4	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	30.0	2.069605E-7	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	30.0	2.069605E-8	g	
Sub-Item	1	30 50/50 GRID DRST RCPT HSG				1.0	0.2648118	g	
Material	2	LCP-GF35				1.0	0.2648118	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	2.0	1.0	0.00529624	g	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	34.3	1.0	0.09083045	g	
Substance	3	1,3-Benzenedicarboxylic acid, polymer with 1,4-benzenedicarboxylic acid, [1,1-biphenyl]-4,4-diol and 4-hydroxybenzoic acid	Supplier	60088-52-0	62.7	1.0	0.166037	g	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	0.00264812	g	
Sub-Item	1	50/50 GRID STND HLDWN PLTD				2.0	0.02921274	g	
Material	2	Beryllium Copper				2.0	0.028637	g	
Substance	3	Beryllium	Supplier	7440-41-7	2.0	2.0	5.7274E-4	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	2.8637E-6	g	
Substance	3	Manganese	Supplier	7439-96-5	0.02	2.0	5.7274E-6	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.2	2.0	5.7274E-5	g	
Substance	3	Silicon	Supplier	7440-21-3	0.2	2.0	5.7274E-5	g	
Substance	3	Iron	Supplier	7439-89-6	0.4	2.0	1.1455E-4	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	2.8637E-6	g	
Substance	3	Aluminum	Supplier	7429-90-5	0.2	2.0	5.7274E-5	g	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	2.0	2.8637E-7	g	
Substance	3	Copper	Supplier	7440-50-8	96.6535	2.0	0.02767866	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	2.8637E-5	g	
Substance	3	Nickel	Nickel	7440-02-0	0.2	2.0	5.7274E-5	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	2.0	1.43185E-6	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	1.43185E-7	g	
Material	2	Nickel Plate				2.0	2.3408E-4	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.0	4.681618E-7	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	2.340809E-7	g	
Substance	3	Nickel	Nickel	7440-02-0	99.7	2.0	2.3338E-4	g	
Material	2	Tin-Lead Plate				2.0	3.4166E-4	g	
Substance	3	Tin	Supplier	7440-31-5	86.5	2.0	2.9554E-4	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.5	2.0	1.7083E-6	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	13.0	2.0	4.44158E-5	g	