



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	John Penica	<b>Contact Title</b>	Sr Mgr Engineering, IND Central Eng		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2018-03-05	<b>Contact Email</b>	jrpenica@te.com				
<b>Contact Phone Number</b>	+1-717-592-3266								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	1-215570-6	<b>Amount</b>	959.586112	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	MICRO-MATCH PBC.16P	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUROHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-0117</b>	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
<b>Complex Article Description</b>	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	MICRO-MATCH M COVER				1.0	156.32	mg	
Material	2	PBT-GF20-FR(17)				1.0	156.32	mg	
Substance	3	Lead oxide (lead monoxide)	Lead/Lead Compounds	1317-36-8	0.0020	1.0	0.0031264	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.5	1.0	0.7816	mg	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.1	1.0	0.15632	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	39.08	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	17.0	1.0	26.5744	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	1.0	4.6896	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.2	1.0	0.31264	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	0.5	1.0	0.7816	mg	

Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	46.896	1.0	73.30783	mg	
Substance	3	Zinc sulfide (ZnS)	Supplier	1314-98-3	1.0	1.0	1.5632	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	7.816	mg	
Substance	3	Benzenesulfonic acid, 4,5-dichloro-2-[2-[4,5-dihydro-3-methyl-5-oxo-1-(3-sulfophenyl)-1H-pyrazol-4-yl]diazonyl]-, calcium salt (1:1)	Supplier	65212-77-3	0.8	1.0	1.25056	mg	
Substance	3	Arsenic oxide (As2O3)	Arsenic oxide (As2O3)	1327-53-3	0.0020	1.0	0.0031264	mg	
Sub-Item	1	MICRO-MATCH P.B.HSG				1.0	316.92	mg	
Material	2	PBT-GF20-FR(17)				1.0	316.92	mg	
Substance	3	Lead oxide (lead monoxide)	Lead/Lead Compounds	1317-36-8	0.0020	1.0	0.0063384	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.5	1.0	1.5846	mg	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.1	1.0	0.31692	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	79.23	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	17.0	1.0	53.8764	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	1.0	9.5076	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.2	1.0	0.63384	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	0.5	1.0	1.5846	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	46.896	1.0	148.6228	mg	
Substance	3	Zinc sulfide (ZnS)	Supplier	1314-98-3	1.0	1.0	3.1692	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	15.846	mg	
Substance	3	Benzenesulfonic acid, 4,5-dichloro-2-[2-[4,5-dihydro-3-methyl-5-oxo-1-(3-sulfophenyl)-1H-pyrazol-4-yl]diazonyl]-, calcium salt (1:1)	Supplier	65212-77-3	0.8	1.0	2.53536	mg	
Substance	3	Arsenic oxide (As2O3)	Arsenic oxide (As2O3)	1327-53-3	0.0020	1.0	0.0063384	mg	
Sub-Item	1	MICRO MATCH PB CONT				16.0	30.396632	mg	
Material	2	Phos Bronze				16.0	30.1	mg	

Substance	3	Copper	Supplier	7440-50-8	94.6985	16.0	28.50425	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	16.0	0.00602	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	16.0	0.00301	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	16.0	1.3545	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	16.0	0.001505	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	16.0	0.0301	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	16.0	0.00301	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	16.0	3.01E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	16.0	0.0903	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	16.0	0.0301	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	16.0	0.0301	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	16.0	0.001505	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	16.0	0.01505	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	16.0	0.0301	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	16.0	1.505E-4	mg	
Material	2	Nickel Plate				16.0	0.114132	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	16.0	2.2826E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	16.0	1.1413E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	16.0	0.11379	mg	
Material	2	Tin Plate				16.0	0.1825	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	16.0	3.65E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	16.0	0.18201	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	16.0	1.2775E-4	mg	