



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Staff Mfg & Process Dvl Engineer		
Company Unique ID	TE Connectivity	Response Date	2018-04-03	Contact Email	dave.benfer@te.com				
Contact Phone Number	+1-717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1-5227079-9	Amount	8295.11593495	Version	-	Identity			
Manufacturer Item Name	COMM BNC PLUG	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirements by application of the selected exemption(s)								
ChinaRoHS-0508	Product(s) is NOT eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	CONTACT, BNC, PLTD				1.0	137.545	mg	
Material	2	Brass				1.0	136.0	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.00136	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.0136	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.136	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.0136	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.0272	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.00136	mg	
Substance	3	Iron	Supplier	7439-89-6	0.35	1.0	0.476	mg	
Substance	3	Zinc	Supplier	7440-66-6	32.7475	1.0	44.5366	mg	
Substance	3	Copper	Supplier	7440-50-8	63.0	1.0	85.68	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	6.8E-4	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.0136	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	3.7	1.0	5.032	mg	6(c) Lead as an alloying element in copper containing up to 4% lead by weight
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.068	mg	
Material	2	Nickel Plate				1.0	0.521	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.001042	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	5.21E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	0.51944	mg	
Material	2	Gold Plate				1.0	1.024	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	1.02093	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	1.0	0.003072	mg	

Sub-Item	1	FERRULE, PLTD, LEAD FREE				1.0	308.527797	mg	
Material	2	Tin Plate				1.0	1.291632	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	1.28814	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.00258326	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	9.0414E-4	mg	
Material	2	Copper				1.0	307.236165	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.15362	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.00307236	mg	
Substance	3	Copper	Supplier	7440-50-8	99.7575	1.0	306.49112	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.00307236	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	1.0	0.01536181	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.03072362	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.06144723	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.30724	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.15362	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00153618	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.01536181	mg	
Sub-Item	1	PLUG ASSY, COML BNC				1.0	7849.04313795	mg	
Material	2	Stainless Steel				1.0	146.0	mg	
Substance	3	Chromium	Supplier	7440-47-3	18.0	1.0	26.28	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.5	1.0	0.73	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.045	1.0	0.0657	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.0146	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.15	1.0	0.219	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.01	1.0	0.0146	mg	
Substance	3	Silicon	Supplier	7440-21-3	1.5	1.0	2.19	mg	
Substance	3	Manganese	Supplier	7439-96-5	2.0	1.0	2.92	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.03	1.0	0.0438	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.03	1.0	0.0438	mg	
Substance	3	Iron	Supplier	7439-89-6	68.6147	1.0	100.17746	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	0.14585	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0099	1.0	0.014454	mg	
Substance	3	Nickel	Nickel	7440-02-0	9.0	1.0	13.14	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	7.3E-4	mg	
Material	2	Brass				1.0	594.0	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.00594	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	1.0	166.45365	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	1.0	0.297	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.0594	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	1.0	0.297	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.594	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	1.0	424.71	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.00594	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.0594	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00297	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	1.0	1.188	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.0297	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.297	mg	
Material	2	SILICONE				1.0	13.0	mg	
Substance	3	Iron oxide (Fe2O3)	Supplier	1309-37-1	5.0	1.0	0.65	mg	
Substance	3	Siloxanes and Silicones, di-Me, vinyl group-terminated	Supplier	68083-19-2	14.0	1.0	1.82	mg	
Substance	3	Silica gel, pptd., cryst.-free	Supplier	112926-00-8	11.0	1.0	1.43	mg	

Substance	3	Siloxanes and Silicones, di-Me, hydrogen-terminated, reaction products with epichlorohydrin ; formaldehyde-phenol polymer and [(2-propenyloxy)methyl]oxirane	Supplier	218163-11-2	70.0	1.0	9.1	mg	
Material	2	Zinc Alloy				1.0	3891.3	mg	
Substance	3	Iron	Supplier	7439-89-6	0.08	1.0	3.11304	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.38913	mg	
Substance	3	Zinc	Supplier	7440-66-6	95.1925	1.0	3704.22575	mg	
Substance	3	Copper	Supplier	7440-50-8	0.25	1.0	9.72825	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.038913	mg	
Substance	3	Magnesium	Supplier	7439-95-4	0.02	1.0	0.77826	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.01	1.0	0.38913	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.38913	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.038913	mg	
Substance	3	Aluminum	Supplier	7429-90-5	4.3	1.0	167.3259	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	3.8913	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0030	1.0	0.11674	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0020	1.0	0.077826	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0194565	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.02	1.0	0.77826	mg	
Material	2	Brass				1.0	1232.87	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.0123287	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.12329	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	1.23287	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.12329	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.24657	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.0123287	mg	
Substance	3	Iron	Supplier	7439-89-6	0.35	1.0	4.31504	mg	
Substance	3	Zinc	Supplier	7440-66-6	32.7475	1.0	403.7341	mg	
Substance	3	Copper	Supplier	7440-50-8	63.0	1.0	776.7081	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00616435	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.12329	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	3.7	1.0	45.61619	mg	6(c) Lead as an alloying element in copper containing up to 4% lead by weight
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.61643	mg	
Material	2	Nickel Plate				1.0	59.210283	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.05921028	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	59.03265	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.11842	mg	
Material	2	Copper Plate				1.0	81.177181	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.08117718	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	81.096	mg	
Material	2	Tri Chrome Film				1.0	0.18567395	mg	
Substance	3	Silicate(2-), hexafluoro-, hydrogen (1:2)	Supplier	16961-83-4	30.0	1.0	0.05570218	mg	
Substance	3	Chromium chloride (CrCl3), hydrate (1:6)	Supplier	10060-12-5	60.0	1.0	0.1114	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	10.0	1.0	0.01856739	mg	
Material	2	Brass				1.0	1494.3	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0074715	mg	

Substance	3	Zinc	Supplier	7440-66-6	8.5175	1.0	127.277	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	1.4943	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.014943	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.14943	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.14943	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	1.0	0.74715	mg	
Substance	3	Copper	Supplier	7440-50-8	91.0	1.0	1359.813	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.014943	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	1.0	0.74715	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	1.0	2.9886	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.14943	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.74715	mg	
Material	2	Unspecified Compliant Material				1.0	337.0	mg	
Substance	3	Unspecified ROHS Compliant Substance	Supplier	Unspecified Compliant Substance	100.0	1.0	337.0	mg	