



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer David W	Contact Title	Product Compliance Engineer for DND		
Company Unique ID	TE Connectivity	Response Date	2018-04-04	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1658657-1	Amount	40964.50457	Version	-	Identity			
Manufacturer Item Name	KIT,HDP-20,ENCLSUR,PLUG,SIZE 2	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	HDP-20,OVRMLD PLUG SUBASSY,SIZ				1.0	6152.62769	mg	
Material	2	Copper Plate				1.0	110.36699	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.11037	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	110.25662	mg	
Material	2	Carbon Steel				1.0	1563.0	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.007815	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.1563	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.6	1.0	9.378	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.13	1.0	2.0319	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.04	1.0	0.6252	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.15	1.0	2.3445	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.01563	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.02	1.0	0.3126	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.1	1.0	1.563	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	1.563	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0099	1.0	0.15474	mg	
Substance	3	Iron	Supplier	7439-89-6	98.6837	1.0	1542.42623	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	1.56144	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.07815	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.7815	mg	
Material	2	PA66-GF25FR(52)				1.0	1029.0	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	257.25	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediy)]imino-1,6-hexanediy]	Supplier	32131-17-2	58.0	1.0	596.82	mg	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.6	1.0	37.044	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	11.0	1.0	113.19	mg	
Substance	3	Benzenamine, reaction products with aniline hydrochloride and nitrobenzene	Supplier	101357-15-7	2.4	1.0	24.696	mg	
Material	2	Carbon Steel				1.0	2271.5	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.08	1.0	1.8172	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.02	1.0	0.4543	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.02	1.0	0.4543	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.22715	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.02	1.0	0.4543	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.15	1.0	3.40725	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	2.2715	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.22715	mg	
Substance	3	Molybdenum	Supplier	7439-98-7	0.75	1.0	17.03625	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.4	1.0	9.086	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.1	1.0	2.2715	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.022715	mg	
Substance	3	Iron	Supplier	7439-89-6	98.1785	1.0	2230.12463	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	1.13575	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.22715	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0113575	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	2.2715	mg	
Material	2	PBT-I-GF30-FR(17)				1.0	1022.0	mg	
Substance	3	Dolomite (CaMg(CO3)2)	Supplier	16389-88-1	0.5	1.0	5.11	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	35.0	1.0	357.7	mg	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	1.0	2.044	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.2	1.0	2.044	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	1.0	30.66	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	2.0	1.0	20.44	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	1.0	1.0	10.22	mg	
Substance	3	Chlorite-group minerals	Supplier	1318-59-8	0.5	1.0	5.11	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	10.22	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	36.6	1.0	374.052	mg	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	1.0	5.11	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	18.0	1.0	183.96	mg	
Substance	3	Quartz (SiO2)	Supplier	14808-60-7	0.5	1.0	5.11	mg	

Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	1.0	1.0	10.22	mg	
Material	2	Tin Plate				1.0	156.7607	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	0.10973	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.31352	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	156.33745	mg	
Sub-Item	1	HDP SHIELDED INS SHIELD,SN,SZ 2				1.0	3213.47129	mg	
Material	2	Copper Plate				1.0	64.53438	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.06453438	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	64.46985	mg	
Material	2	Carbon Steel				1.0	3058.5	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0152925	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.30585	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.6	1.0	18.351	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.13	1.0	3.97605	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.04	1.0	1.2234	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.15	1.0	4.58775	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.030585	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.02	1.0	0.6117	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.1	1.0	3.0585	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	3.0585	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0099	1.0	0.30279	mg	
Substance	3	Iron	Supplier	7439-89-6	98.6837	1.0	3018.24096	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	3.05544	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.15293	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	1.52925	mg	
Material	2	Tin Plate				1.0	90.43691	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	0.06330584	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.18087	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	90.19273	mg	
Sub-Item	1	SHLD JACKSCREW, PLTD				2.0	6478.942	mg	
Material	2	Carbon Steel				2.0	6474.0	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.04	2.0	2.5896	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.6474	mg	
Substance	3	Iron	Supplier	7439-89-6	98.2485	2.0	6360.60789	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.6474	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	6.474	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.05	2.0	3.237	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.06474	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.23	2.0	14.8902	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.15	2.0	9.711	mg	
Substance	3	Manganese	Supplier	7439-96-5	1.0	2.0	64.74	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	2.0	0.6474	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	0.03237	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	6.474	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	2.0	3.237	mg	
Material	2	Zinc Phosphate film				2.0	4.942	mg	
Substance	3	Phosphate	Supplier	14265-44-2	19.6	2.0	0.96863	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	13.5894	2.0	0.67159	mg	
Substance	3	Carbon black	Supplier	1333-86-4	4.9203	2.0	0.24316	mg	

Substance	3	Naphtha (petroleum), hydrotreated light	Supplier	64742-49-0	0.4	2.0	0.019768	mg	
Substance	3	Oxirane, 2,2-[[[(oxiranylmethoxy)phenyl]methylene]bis[(1,1-dimethylethyl)methylphenylene]oxymethylene]]bis-	Supplier	129915-35-1	59.5903	2.0	2.94495	mg	
Substance	3	Zinc	Supplier	7440-66-6	1.9	2.0	0.093898	mg	
Sub-Item	1	HDP SHIELDED OUT SHIELD,SN,SZ 2				1.0	3171.32159	mg	
Material	2	Copper Plate				1.0	61.97349	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.06197349	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	61.91152	mg	
Material	2	Carbon Steel				1.0	3022.5	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0151125	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.30225	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.6	1.0	18.135	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.13	1.0	3.92925	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.04	1.0	1.209	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.15	1.0	4.53375	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.030225	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.02	1.0	0.6045	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.1	1.0	3.0225	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	3.0225	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0099	1.0	0.29923	mg	
Substance	3	Iron	Supplier	7439-89-6	98.6837	1.0	2982.71483	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	1.0	3.01948	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.15113	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	1.51125	mg	
Material	2	Tin Plate				1.0	86.8481	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	0.06079367	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.1737	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	86.61361	mg	
Sub-Item	1	15 SHIELD ENCLOSURE HDP				1.0	15469.2	mg	
Material	2	POLYVINYL CHLORIDE				1.0	15469.2	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	1.0	46.4076	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	1.8	1.0	278.4456	mg	
Substance	3	Barium	Supplier	7440-39-3	0.6	1.0	92.8152	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	4.34	1.0	671.36328	mg	
Substance	3	Hexanedioic acid, 1,6-bis(2-ethylhexyl) ester	Supplier	103-23-1	20.2	1.0	3124.7784	mg	
Substance	3	Ethene, chloro-, homopolymer	Supplier	9002-86-2	72.4	1.0	11199.7008	mg	
Substance	3	1,2-Benzenedicarboxylic acid, 1,2-diisodecyl ester	Phthalates (DINP, DIDP, DNOP)	26761-40-0	0.36	1.0	55.68912	mg	