



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Wu, Cc	<b>Contact Title</b>	Prod Compliance Engineer		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2017-11-06	<b>Contact Email</b>	cc.wu@te.com				
<b>Contact Phone Number</b>	86-2124071672								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	1-770873-1	<b>Amount</b>	1132.529	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	03P MINI UMNL HDR ASSY AU LF	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-0117</b>	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
<b>Complex Article Description</b>	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	03P MINI UMNL HDR HSG CLSD BTM				1.0	803.0	mg	
Material	2	PA				1.0	803.0	mg	
Substance	3	Water	Supplier	7732-18-5	0.3262	1.0	2.61939	mg	
Substance	3	2H-Azepin-2-one, hexahydro-	Supplier	105-60-2	0.4637	1.0	3.72351	mg	
Substance	3	Siloxanes and Silicones, di-Me	Supplier	63148-62-9	3.0E-4	1.0	0.002409	mg	
Substance	3	Poly[[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	0.9451	1.0	7.58915	mg	
Substance	3	Benzenepropanamide, N,N-1,6-hexanediylbis[3,5-bis(1,1-dimethylethyl)-4-hydroxy-	Supplier	23128-74-7	0.4004	1.0	3.21521	mg	
Substance	3	1,2-Ethanediamine	Supplier	107-15-3	0.0033	1.0	0.026499	mg	
Substance	3	Phosphoric acid, sodium salt, hydrate (1:2:12)	Supplier	10039-32-4	0.025	1.0	0.20075	mg	
Substance	3	Octadecanoic acid, calcium salt (2:1)	Supplier	1592-23-0	0.2012	1.0	1.61564	mg	
Substance	3	Octadecanamide, N,N-1,2-ethanediylbis-	Supplier	110-30-5	0.1901	1.0	1.5265	mg	
Substance	3	1,3,5-Triazine-2,4,6-(1H,3H,5H)-trione, compd. with 1,3,5-triazine-2,4,6-triamine (1:1)	Supplier	37640-57-6	9.0717	1.0	72.84575	mg	

Substance	3	Hexanedioic acid, polymer with hexahydro-2H-azepin-2-one and 1,6-hexanediamine	Supplier	24993-04-2	88.373	1.0	709.63519	mg	
Sub-Item	1	MINI UMNL BAND PIN SNAU LF				3.0	109.843	mg	
Material	2	Gold Plate				3.0	0.273	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	1.0	3.0	0.00273	mg	
Substance	3	Gold	Supplier	7440-57-5	99.0	3.0	0.27027	mg	
Material	2	Tin Plate				3.0	0.923	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	3.0	0.92051	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	3.0	0.001846	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	3.0	6.461E-4	mg	
Material	2	Brass Wire				3.0	108.0	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	3.0	77.22	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	3.0	0.00108	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0226	3.0	30.26441	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	3.0	0.054	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	3.0	0.00108	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	3.0	0.054	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	3.0	0.108	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0099	3.0	0.010692	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	3.0	0.0108	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	3.0	0.054	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	3.0	0.0054	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	3.0	5.4E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	3.0	0.216	mg	
Material	2	Nickel Plate				3.0	0.647	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	3.0	0.001294	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	3.0	6.47E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	3.0	0.64506	mg	