



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	TE Product Compliance	Contact Title	-		
Company Unique ID	TE Connectivity	Response Date	2018-08-02	Contact Email	productcompliance@te.com				
Contact Phone Number	+001-800-522-6752								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1734774-4	Amount	2539.504	Version	-	Identity			
Manufacturer Item Name	PCI EXP 3.1L 36 POS BLK 15u"	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Material	1	CONTACTS_Sn_Plating				1.0	1.62	mg	
Substance	2	Tin	Supplier	7440-31-5	99.9	1.0	1.61838	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.1	1.0	0.00162	mg	
Material	1	CONTACTS_Au_Plating				1.0	0.36	mg	
Substance	2	Gold	Supplier	7440-57-5	99.9	1.0	0.35964	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.1	1.0	3.6E-4	mg	
Material	1	CONTACTS_Cu_Alloy				1.0	483.6	mg	
Substance	2	Phosphorus	Supplier	7723-14-0	0.35	1.0	1.6926	mg	
Substance	2	Iron	Supplier	7439-89-6	0.1	1.0	0.4836	mg	
Substance	2	Copper	Supplier	7440-50-8	92.55	1.0	447.5718	mg	
Substance	2	Tin	Supplier	7440-31-5	6.75	1.0	32.643	mg	
Substance	2	Zinc	Supplier	7440-66-6	0.2	1.0	0.9672	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.2418	mg	
Material	1	CONTACTS_Ni_Plating				1.0	3.924	mg	
Substance	2	Nickel	Nickel	7440-02-0	99.8	1.0	3.91615	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.007848	mg	
Material	1	HOUSING_PA9T				1.0	2050.0	mg	
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	33.0	1.0	676.5	mg	
Substance	2	Antimony oxide (Sb2O3)	Supplier	1309-64-4	3.0	1.0	61.5	mg	

Substance	2	1,4-Benzenedicarboxylic acid, polymer with 2-methyl-1,8-octanediamine and 1,9-nonanediamine	Supplier	169284-22-4	42.0	1.0	861.0	mg	
Substance	2	Benzene, ethenyl-, homopolymer, brominated	Supplier	88497-56-7	22.0	1.0	451.0	mg	