



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer David W	Contact Title	Product Compliance Engineer for DND		
Company Unique ID	TE Connectivity	Response Date	2018-07-10	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	207345-1	Amount	14749.14	Version	-	Identity			
Manufacturer Item Name	CABLE CLAMP KIT,SZ 3	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE Contained in the Product Above the Limits per the Definition within REACH								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	AMPLIMITE SIZE 3 CABLE GATES				1.0	2566.0	mg	
Material	2	PP				1.0	2514.68	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	4.0	1.0	100.5872	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	1.0	1.0	25.1468	mg	
Substance	3	Carbon black	Supplier	1333-86-4	2.0	1.0	50.2936	mg	
Substance	3	Polypropylene - ISO 1043-1 Term PP	Supplier	1043-1-PP	86.0	1.0	2162.6248	mg	
Substance	3	Benzene, 1,1-(1-methylethylidene)bis[3,5-dibromo-4-(2,3-dibromopropoxy)-]	Brominated Flame Retardants (other than PBBs or PBDEs)	21850-44-2	7.0	1.0	176.0276	mg	
Material	2	FOAM PE MB				1.0	51.32	mg	
Substance	3	Octadecanoic acid, zinc salt (2:1)	Supplier	557-05-1	2.14	1.0	1.09825	mg	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.73	1.0	0.37464	mg	
Substance	3	Diazene-1,2-dicarboxamide (C,C-azodi(formamide))	Supplier	123-77-3	10.71	1.0	5.49637	mg	
Substance	3	Silica	Supplier	7631-86-9	0.5355	1.0	0.27482	mg	

Substance	3	Ethene, homopolymer	Supplier	9002-88-4	85.1545	1.0	43.70129	mg	
Substance	3	Propanoic acid, 3,3-thiobis-, 1,1-dioctadecyl ester	Supplier	693-36-7	0.73	1.0	0.37464	mg	
Sub-Item	1	SELF TAPPING SCREW,ZN				3.0	643.38	mg	
Material	2	Carbon Steel				3.0	632.4	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.04	3.0	0.25296	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	3.0	0.06324	mg	
Substance	3	Iron	Supplier	7439-89-6	98.2485	3.0	621.32351	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	3.0	0.06324	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	3.0	0.6324	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.05	3.0	0.3162	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	3.0	0.006324	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.23	3.0	1.45452	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.15	3.0	0.9486	mg	
Substance	3	Manganese	Supplier	7439-96-5	1.0	3.0	6.324	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	3.0	0.06324	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	3.0	0.003162	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	3.0	0.6324	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	3.0	0.3162	mg	
Material	2	Zinc Phosphate film				3.0	10.98	mg	
Substance	3	Phosphate	Supplier	14265-44-2	19.6	3.0	2.15208	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	13.5894	3.0	1.49212	mg	
Substance	3	Carbon black	Supplier	1333-86-4	4.9203	3.0	0.54025	mg	
Substance	3	Naphtha (petroleum), hydrotreated light	Supplier	64742-49-0	0.4	3.0	0.04392	mg	
Substance	3	Oxirane, 2,2-[[[(oxiranyl)methoxy]phenyl]methylene]bis[[1,1-dimethylethyl)methylphenylene]oxymethylene]bis-	Supplier	129915-35-1	59.5903	3.0	6.54301	mg	
Substance	3	Zinc	Supplier	7440-66-6	1.9	3.0	0.20862	mg	
Sub-Item	1	AMPLIMITE CABLE CLAMP HSG SZ 3				1.0	10253.0	mg	
Material	2	PP				1.0	10047.94	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	4.0	1.0	401.9176	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0506	1.0	1.0	100.4794	mg	
Substance	3	Carbon black	Supplier	1333-86-4	2.0	1.0	200.9588	mg	
Substance	3	Polypropylene - ISO 1043-1 Term PP	Supplier	1043-1-PP	86.0	1.0	8641.2284	mg	
Substance	3	Benzene, 1,1-(1-methylethylidene)bis[3,5-dibromo-4-(2,3-dibromopropoxy)-]	Brominated Flame Retardants (other than PBBs or PBDEs)	21850-44-2	7.0	1.0	703.3558	mg	
Material	2	FOAM PE MB				1.0	205.06	mg	
Substance	3	Octadecanoic acid, zinc salt (2:1)	Supplier	557-05-1	2.14	1.0	4.38828	mg	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.73	1.0	1.49694	mg	

Substance	3	Diazene-1,2-dicarboxamide (C,C-azodi(formamide))	Supplier	123-77-3	10.71	1.0	21.96193	mg	
Substance	3	Silica	Supplier	7631-86-9	0.5355	1.0	1.0981	mg	
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	85.1545	1.0	174.61782	mg	
Substance	3	Propanoic acid, 3,3-thiobis-, 1,1-dioctadecyl ester	Supplier	693-36-7	0.73	1.0	1.49694	mg	