



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Staff Mfg & Process Dvl Engineer		
Company Unique ID	TE Connectivity	Response Date	2017-09-06	Contact Email	dave.benfer@te.com				
Contact Phone Number	+1-717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	226990-1	Amount	9.6219209	Version	-	Identity			
Manufacturer Item Name	RTANG JACK, BNC PCB	Weight Uom	g	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	POST BNC PCB, LEAD-FREE, .869				1.0	0.07723493	g	
Material	2	Nickel Plate				1.0	8.5068E-4	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	1.701356E-6	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	8.50678E-7	g	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	8.4813E-4	g	
Material	2	Tin Plate				1.0	0.00162625	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	3.252498E-6	g	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	0.00162186	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	1.138374E-6	g	
Material	2	Brass Wire				1.0	0.074758	g	
Substance	3	Copper	Supplier	7440-50-8	71.5	1.0	0.05345197	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	7.4758E-7	g	
Substance	3	Zinc	Supplier	7440-66-6	28.0226	1.0	0.02094914	g	
Substance	3	Manganese	Supplier	7439-96-5	0.05	1.0	3.7379E-5	g	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	7.4758E-7	g	
Substance	3	Iron	Supplier	7439-89-6	0.05	1.0	3.7379E-5	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	7.4758E-5	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.0099	1.0	7.401042E-6	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	7.4758E-6	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	3.7379E-5	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	3.7379E-6	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	3.7379E-7	g	
Substance	3	Nickel	Nickel	7440-02-0	0.2	1.0	1.4952E-4	g	
Sub-Item	1	DIELECTRIC, S ER BNC				1.0	0.3632269	g	
Material	2	PMP				1.0	0.3632269	g	

Substance	3	1-Octadecene, polymer with 1-hexadecene and 4-methyl-1-pentene	Supplier	81229-87-0	99.0	1.0	0.35959463	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	1.0	1.0	0.00363227	g	
Sub-Item	1	CONTACT,RT ANG,SERIES BNC, LEAD				1.0	0.20628767	g	
Material	2	Nickel Plate				1.0	0.00419089	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	8.381776E-6	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	4.190888E-6	g	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	0.00417832	g	
Material	2	Phos Bronze				1.0	0.1997	g	
Substance	3	Copper	Supplier	7440-50-8	94.6985	1.0	0.1891129	g	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	3.994E-5	g	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	1.997E-5	g	
Substance	3	Tin	Supplier	7440-31-5	4.5	1.0	0.0089865	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	1.0	9.985E-6	g	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	1.997E-4	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	1.997E-5	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	1.997E-6	g	
Substance	3	Zinc	Supplier	7440-66-6	0.3	1.0	5.991E-4	g	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	1.0	1.997E-4	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	1.997E-4	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	9.985E-6	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	9.985E-5	g	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	1.997E-4	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	9.985E-7	g	
Material	2	Tin Plate				1.0	0.00239678	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	4.79356E-6	g	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	0.00239031	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	1.677746E-6	g	
Sub-Item	1	HOUSING,ST D,JACK,PCB,BNC-TNC				1.0	2.7463	g	
Material	2	PBT-GF15				1.0	2.7463	g	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.9	1.0	0.0247167	g	
Substance	3	Acetic acid ethenyl ester, polymer with ethene	Supplier	24937-78-8	2.5	1.0	0.0686575	g	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	0.137315	g	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.1	1.0	0.0027463	g	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.3	1.0	0.0082389	g	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.5	1.0	0.0137315	g	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	57.8	1.0	1.5873614	g	

Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	0.4	1.0	0.0109852	g	
Substance	3	Octadecanoic acid, 1,1-[2,2-bis[[1-(oxooctadecyl)oxy]methyl]-1,3-propanediyl] ester	Supplier	115-83-3	0.5	1.0	0.0137315	g	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	17.0	1.0	0.466871	g	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol], bis(2,4,6-tribromophenyl) ester	Brominated Flame Retardants (other than PBBs or PBDEs)	71342-77-3	15.0	1.0	0.411945	g	
Sub-Item	1	BNC,PCB,SHELL				1.0	6.2288714	g	
Material	2	Nickel Plate				1.0	0.0546	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	5.46E-5	g	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	0.0544362	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	1.092E-4	g	
Material	2	Copper Plate				1.0	0.073045	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	7.3045E-5	g	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	0.07297195	g	
Material	2	Tri Chrome Film				1.0	2.264E-4	g	
Substance	3	Silicate(2-), hexafluoro-, hydrogen (1:2)	Supplier	16961-83-4	30.0	1.0	6.792E-5	g	
Substance	3	Chromium chloride (CrCl3), hydrate (1:6)	Supplier	10060-12-5	60.0	1.0	1.3584E-4	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	10.0	1.0	2.264E-5	g	
Material	2	Zinc Alloy				1.0	6.101	g	
Substance	3	Silicon	Supplier	7440-21-3	0.035	1.0	0.00213535	g	
Substance	3	Chromium	Supplier	7440-47-3	0.02	1.0	0.0012202	g	
Substance	3	Tin	Supplier	7440-31-5	0.0030	1.0	1.8303E-4	g	
Substance	3	Manganese	Supplier	7439-96-5	0.06	1.0	0.0036606	g	
Substance	3	Copper	Supplier	7440-50-8	0.25	1.0	0.0152525	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	6.101E-4	g	
Substance	3	Zinc	Supplier	7440-66-6	95.0315	1.0	5.79787181	g	
Substance	3	Aluminum	Supplier	7429-90-5	4.3	1.0	0.262343	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	6.101E-4	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	6.101E-5	g	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	0.006101	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.006101	g	
Substance	3	Magnesium	Supplier	7439-95-4	0.05	1.0	0.0030505	g	
Substance	3	Nickel	Nickel	7440-02-0	0.02	1.0	0.0012202	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0050	1.0	3.0505E-4	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	3.0505E-5	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0040	1.0	2.4404E-4	g	