



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer for DND		
Company Unique ID	TE Connectivity	Response Date	2018-01-12	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1565357-1	Amount	733.4	Version	-	Identity			
Manufacturer Item Name	ON TAPING(EMBOS S)0.5MM PITCH B	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	RECEPTACLE ASSEMBLY FOR 0.5MM				1.0	733.4	mg	
Material	2	Phos Bronze				1.0	456.2	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	1.0	432.01456	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.09124	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.04562	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	1.0	20.529	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	1.0	0.02281	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	0.4562	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.04562	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.004562	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	1.0	1.3686	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	1.0	0.4562	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.4562	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.02281	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.2281	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	0.4562	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.002281	mg	
Material	2	Nickel Plate				1.0	6.0	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.0060	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	5.982	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.012	mg	
Material	2	Tin Plate				1.0	0.4	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	8.0E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	0.39892	mg	

Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	2.8E-4	mg	
Material	2	Gold Plate				1.0	1.8	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	1.7946	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	1.0	0.0054	mg	
Material	2	PA9T-GF30				1.0	269.0	mg	
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	0.3	1.0	0.807	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	4.2	1.0	11.298	mg	
Substance	3	Carbon black	Supplier	1333-86-4	0.2	1.0	0.538	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.7	1.0	1.883	mg	
Substance	3	Benzene, ethenyl-, homopolymer, brominated	Supplier	88497-56-7	19.8	1.0	53.262	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	29.8	1.0	80.162	mg	
Substance	3	1,4-Benzenedicarboxylic acid, polymer with 2-methyl-1,8-octanediamine and 1,9-nonanediamine	Supplier	169284-22-4	45.0	1.0	121.05	mg	