



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Benfer David W	<b>Contact Title</b>	Product Compliance Engineer for DND		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2018-04-18	<b>Contact Email</b>	dave.benfer@te.com				
<b>Contact Phone Number</b>	717-986-3725								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	1658686-2	<b>Amount</b>	88.6606	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	SOCKET CONT, 22-28 AWG, DF 22, AMPLIMITE	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-0117</b>	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Material	1	Nickel Plate				1.0	1.43	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.00286	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00143	mg	
Substance	2	Nickel	Nickel	7440-02-0	99.7	1.0	1.42571	mg	
Material	1	Gold Plate				1.0	0.1196	mg	
Substance	2	Gold	Supplier	7440-57-5	99.7	1.0	0.11924	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	1.0	3.588E-4	mg	
Material	1	Phos Bronze				1.0	86.3	mg	
Substance	2	Copper	Supplier	7440-50-8	94.6985	1.0	81.72481	mg	
Substance	2	Manganese	Supplier	7439-96-5	0.02	1.0	0.01726	mg	
Substance	2	Chromium	Supplier	7440-47-3	0.01	1.0	0.00863	mg	
Substance	2	Tin	Supplier	7440-31-5	4.5	1.0	3.8835	mg	
Substance	2	Arsenic	Supplier	7440-38-2	0.0050	1.0	0.004315	mg	
Substance	2	Iron	Supplier	7439-89-6	0.1	1.0	0.0863	mg	
Substance	2	Antimony	Supplier	7440-36-0	0.01	1.0	0.00863	mg	
Substance	2	Beryllium	Supplier	7440-41-7	0.0010	1.0	8.63E-4	mg	
Substance	2	Zinc	Supplier	7440-66-6	0.3	1.0	0.2589	mg	
Substance	2	Phosphorus	Supplier	7723-14-0	0.1	1.0	0.0863	mg	
Substance	2	Cobalt	Supplier	7440-48-4	0.1	1.0	0.0863	mg	
Substance	2	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.004315	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.04315	mg	
Substance	2	Nickel	Nickel	7440-02-0	0.1	1.0	0.0863	mg	
Substance	2	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	4.315E-4	mg	
Material	1	Tin Plate				1.0	0.811	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.001622	mg	
Substance	2	Tin	Supplier	7440-31-5	99.73	1.0	0.80881	mg	

Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	5.677E-4	mg	
-----------	---	------	---------------------	-----------	------	-----	----------	----	--