



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Cc Wu	Contact Title	Product Compliance Engineer		
Company Unique ID	TE Connectivity	Response Date	2017-12-19	Contact Email	cc.wu@te.com				
Contact Phone Number	86-2124071672								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	2-1445098-3	Amount	441.991701	Version	-	Identity			
Manufacturer Item Name	MICRO MNL HDR ASSY S/ROW AU LF	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	MICRO MNL HDR HSG SINGLE ROW				1.0	306.6	mg	
Material	2	PA4T-GF30-FR(40)				1.0	306.6	mg	
Substance	3	Carbon black	Supplier	1333-86-4	0.9	1.0	2.7594	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	91.98	mg	
Substance	3	Polyamide 4T - ISO 1043-1 Term PA4T	Supplier	1043-1-PA4T	47.1	1.0	144.4086	mg	
Substance	3	Halogen-free organic phosphorus flame retardant - ISO 1043-4 code #FR(40)	Supplier	1043-4-FR40	12.0	1.0	36.792	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	10.0	1.0	30.66	mg	
Sub-Item	1	Post Contact right angle lower				3.0	45.130567	mg	
Material	2	Nickel Plate				3.0	0.600592	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	3.0	0.00120118	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	3.0	6.0059E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	3.0	0.59879	mg	
Material	2	Tin Plate				3.0	0.430879	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	3.0	0.42972	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	3.0	8.6176E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	3.0	3.0162E-4	mg	
Material	2	Brass				3.0	43.948744	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	3.0	4.3949E-4	mg	

Substance	3	Zinc	Supplier	7440-66-6	28.0225	3.0	12.31554	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	3.0	0.02197437	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	3.0	0.00439487	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	3.0	0.02197437	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	3.0	0.04394874	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	3.0	31.42335	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	3.0	4.3949E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	3.0	0.00439487	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	3.0	2.1974E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	3.0	0.08789749	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	3.0	0.00219744	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	3.0	0.02197437	mg	
Material	2	Gold Plate				3.0	0.150352	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	3.0	0.1499	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	3.0	4.5106E-4	mg	