



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Penica, John R	Contact Title	Sr Mgr Engineering, IND Central Eng																											
Company Unique ID	TE Connectivity	Response Date	2018-03-23	Contact Email	jrpenica@te.com																													
Contact Phone Number		+1-717-592-3266																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	5-104076-2	Amount	3.3831339	Version	-	Identity																												
Manufacturer Item Name	60 SYS50 HDR DRST SHRD W/SL SN	Weight Uom	g	Mfr Site		Authority																												
Date		UOM	Each																															
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH																																	
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	SYSTEM 50 POST PLTD SN				60.0	0.01170582	g																										
Material	2	Nickel Plate				60.0	2.19E-4	g																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	60.0	4.38E-7	g																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	60.0	2.19E-7	g																										
Substance	3	Nickel	Nickel	7440-02-0	99.7	60.0	2.1834E-4	g																										
Material	2	Gold Plate				60.0	1.721E-4	g																										
Substance	3	Gold	Supplier	7440-57-5	99.7	60.0	1.7158E-4	g																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	60.0	5.163E-7	g																										
Material	2	Gold Flash				60.0	5.87E-6	g																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	60.0	1.761E-8	g																										
Substance	3	Gold	Supplier	7440-57-5	99.7	60.0	5.85239E-6	g																										
Material	2	Brass				60.0	0.01123425	g																										
Substance	3	Tin	Supplier	7440-31-5	0.1	60.0	1.123425E-5	g																										
Substance	3	Copper	Supplier	7440-50-8	64.0	60.0	0.00718992	g																										
Substance	3	Iron	Supplier	7439-89-6	0.05	60.0	5.617125E-6	g																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	60.0	1.123425E-7	g																										
Substance	3	Arsenic	Supplier	7440-38-2	0.01	60.0	1.123425E-6	g																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	60.0	1.123425E-5	g																										
Substance	3	Manganese	Supplier	7439-96-5	0.1	60.0	1.123425E-5	g																										
Substance	3	Zinc	Supplier	7440-66-6	35.2085	60.0	0.00395541	g																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	60.0	1.123425E-6	g																										
Substance	3	Chromium	Supplier	7440-47-3	0.01	60.0	1.123425E-6	g																										
Substance	3	Aluminum	Supplier	7429-90-5	0.05	60.0	5.617125E-6	g																										
Substance	3	Nickel	Nickel	7440-02-0	0.3	60.0	3.370275E-5	g																										
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	60.0	1.123425E-6	g																										

Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	60.0	5.617125E-8	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	60.0	5.617125E-6	g	
Material	2	Tin Plate				60.0	7.46E-5	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	60.0	1.492E-7	g	
Substance	3	Tin	Supplier	7440-31-5	99.73	60.0	7.439858E-5	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	60.0	5.222E-8	g	
Sub-Item	1	60 SYSTEM 50 HDR HSG DR SLOT				1.0	2.6807847	g	
Material	2	LCP-GF35				1.0	2.6807847	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	2.0	1.0	0.05361569	g	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	34.3	1.0	0.91950915	g	
Substance	3	1,3-Benzenedicarboxylic acid, polymer with 1,4-benzenedicarboxylic acid, [1,1-biphenyl]-4,4-diol and 4-hydroxybenzoic acid	Supplier	60088-52-0	62.7	1.0	1.68085201	g	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	0.02680785	g	