



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Wu, Cc	Contact Title	Engineer Product Compliance china		
Company Unique ID	TE Connectivity	Response Date	2018-06-07	Contact Email	cc.wu@te.com				
Contact Phone Number	86-2124071672								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	350759-4	Amount	1485.94	Version	-	Identity			
Manufacturer Item Name	02P UMNL HDR ASSY PC V2 NATL	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	02P UMNL HDR HSG NATL				1.0	1039.0	mg	
Material	2	PA66				1.0	1039.0	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediy)imino-1,6-hexanediy]	Supplier	32131-17-2	99.355	1.0	1032.29845	mg	
Substance	3	Zinc oxide (ZnO)	Supplier	1314-13-2	0.0020	1.0	0.02078	mg	
Substance	3	Octadecanamide, N,N-1,2-ethanediybis-	Supplier	110-30-5	0.3	1.0	3.117	mg	
Substance	3	Water	Supplier	7732-18-5	0.2	1.0	2.078	mg	
Substance	3	Aluminum, hydroxybis(octadecanoato-kappa.O)-	Supplier	300-92-5	0.14	1.0	1.4546	mg	
Substance	3	Siloxanes and Silicones, di-Me	Supplier	63148-62-9	0.0030	1.0	0.03117	mg	
Sub-Item	1	MNL HDR SOK PC PTPPHBZ				2.0	223.47	mg	
Material	2	Phos Bronze				2.0	219.12	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	2.0	207.50335	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	2.0	0.043824	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	2.0	0.021912	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	2.0	9.8604	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	2.0	0.010956	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	2.0	0.21912	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.021912	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.0021912	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	2.0	0.65736	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	2.0	0.21912	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.21912	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	2.0	0.010956	mg	

Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	2.0	0.10956	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	2.0	0.21912	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	0.0010956	mg	
Material	2	Tin Plate				2.0	4.35	mg	
Substance	3	Tin	Supplier	7440-31-5	97.85	2.0	4.25647	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.0	0.0087	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.35	2.0	0.015225	mg	
Substance	3	Copper	Supplier	7440-50-8	1.5	2.0	0.06525	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	0.00435	mg	