



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Manufacturing Info/ Material Info	Subsectionals	D, A
-----------	------------	---------	-----	-----	-----------	------------	-----------------------------------	---------------	------

**Supplier Information**

Company Name	TE Connectivity	Request Document ID		Contact Name	Chan, Nelson	Contact Title	Global Account Manager
Company Unique ID	TE Connectivity	Response Date	2018-06-28	Contact Email	nelson.chan@te.com		
Contact Phone Number	+85227388751						

**Legal Statement**

Supplier Acceptance	true
---------------------	------

**Legal Statement**  
 The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

**Product**

Manufacturer Item number	5-103672-2	Amount	754.3	Version	-	Identity	
Manufacturer Item Name	03 MTE HDR SRR LATCH W/HLDWN	Weight Uom	mg	Mfr Site		Authority	
Date		UOM	Each				

EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed

**Manufacturing Information**

J-STD-020 MSL Rating		Max Total a Wave Time		Ramp Rate		Wave Additional Info	
Classification Temp		Max Wave Solder Time	20.0	Ramp Down Rate		Psi Rating Reflow	
Max Time Within 5		Psi Rating Wave		Package Designator		Size	0.0
Time Above 217		Reflow Additional Info		Preheat Max Temp		Terminal Base Alloy	Not Applicable
Preheat Duration		bulk Solder Termination	Not Applicable	Nbr or Reflow Cycles		Terminal Plating	Not Applicable
Preheat Min Temp		Nbr of Instances	0	Component Temp Spike		Shape	Not Applicable

**Product Disclosure**

Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	03 MTE HDR HSG				1.0	568.0	mg	
Material	2	LCP-GF35				1.0	568.0	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	2.0	1.0	11.36	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	34.3	1.0	194.824	mg	
Substance	3	1,3-benzenedicarb oxylic acid, polymer with 1,4-benzenedicarb oxylic acid, [1,1-biphenyl]-4,4-diol and 4-hydroxybenzoic acid	Supplier	60088-52-0	62.7	1.0	356.136	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	5.68	mg	
Sub-Item	1	MTE POST PLTD LF				3.0	62.1	mg	
Material	2	Tin Plate				3.0	0.62	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	3.0	0.00124	mg	

Substance	3	Tin	Supplier	7440-31-5	99.73	3.0	0.61833	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	3.0	4.34E-4	mg	
Material	2	Nickel Plate				3.0	0.38	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	3.0	7.6E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	3.0	3.8E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	3.0	0.37886	mg	
Material	2	Brass				3.0	61.1	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	3.0	6.11E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	3.0	17.12175	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	3.0	0.03055	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	3.0	0.00611	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	3.0	0.03055	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	3.0	0.0611	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	3.0	43.6865	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	3.0	6.11E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	3.0	0.00611	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	3.0	3.055E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	3.0	0.1222	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	3.0	0.003055	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	3.0	0.03055	mg	