



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																	
Supplier Information																										
Company Name	TE Connectivity	Request Document ID		Contact Name	Penica, John R	Contact Title	Sr Mgr Engineering, IND Central Eng																			
Company Unique ID	TE Connectivity	Response Date	2018-03-16	Contact Email	jrpenica@te.com																					
Contact Phone Number	+1-717-592-3266																									
Legal Statement																										
Supplier Acceptance	true																									
Legal Statement																										
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																										
Product																										
Manufacturer Item number	5-103958-9	Amount	1.62163	Version	-	Identity																				
Manufacturer Item Name	2X10 MTE RCPT SR LATCH .100CL	Weight Uom	g	Mfr Site		Authority																				
Date		UOM	Each																							
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions																									
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																									
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH																									
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed																									
Product Disclosure																										
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																	
Sub-Item	1	MTE RECP 22-26 AWG PLTD 30 SN				10.0	0.087	g																		
Material	2	Phos Bronze				10.0	0.0839	g																		
Substance	3	Copper	Supplier	7440-50-8	94.6985	10.0	0.07945204	g																		
Substance	3	Manganese	Supplier	7439-96-5	0.02	10.0	1.678E-5	g																		
Substance	3	Chromium	Supplier	7440-47-3	0.01	10.0	8.39E-6	g																		
Substance	3	Tin	Supplier	7440-31-5	4.5	10.0	0.0037755	g																		
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	10.0	4.195E-6	g																		
Substance	3	Iron	Supplier	7439-89-6	0.1	10.0	8.39E-5	g																		
Substance	3	Antimony	Supplier	7440-36-0	0.01	10.0	8.39E-6	g																		
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	10.0	8.39E-7	g																		
Substance	3	Zinc	Supplier	7440-66-6	0.3	10.0	2.517E-4	g																		
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	10.0	8.39E-5	g																		
Substance	3	Cobalt	Supplier	7440-48-4	0.1	10.0	8.39E-5	g																		
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	10.0	4.195E-6	g																		
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	10.0	4.195E-5	g																		
Substance	3	Nickel	Nickel	7440-02-0	0.1	10.0	8.39E-5	g																		
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	10.0	4.195E-7	g																		
Material	2	Nickel Plate				10.0	0.0016	g																		
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	10.0	3.2E-6	g																		
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	10.0	1.6E-6	g																		
Substance	3	Nickel	Nickel	7440-02-0	99.7	10.0	0.0015952	g																		
Material	2	Tin Plate				10.0	0.00137	g																		
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	10.0	2.74E-6	g																		
Substance	3	Tin	Supplier	7440-31-5	99.73	10.0	0.0013663	g																		
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	10.0	9.59E-7	g																		

Material	2	Gold Plate				10.0	1.3E-4	g	
Substance	3	Gold	Supplier	7440-57-5	99.7	10.0	1.2961E-4	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	10.0	3.9E-7	g	
Sub-Item	1	10 MTE RCPT HSG SR LATCH .100				1.0	0.75163	g	
Material	2	PBT-GF15				1.0	0.75163	g	
Substance	3	Carbon black	Supplier	1333-86-4	1.5	1.0	0.01127445	g	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.5	1.0	0.00375815	g	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	0.4	1.0	0.00300652	g	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	55.9	1.0	0.42016117	g	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	0.0375815	g	
Substance	3	Acetic acid ethenyl ester, polymer with ethene	Supplier	24937-78-8	3.0	1.0	0.0225489	g	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.9	1.0	0.00676467	g	
Substance	3	Octadecanoic acid, 1,1-[2,2-bis[[[1-oxooctadecyl)oxy]methyl]-1,3-propanediyl] ester	Supplier	115-83-3	0.5	1.0	0.00375815	g	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	17.0	1.0	0.1277771	g	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.3	1.0	0.00225489	g	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and phenol	Brominated Flame Retardants (other than PBBs or PBDEs)	94334-64-2	15.0	1.0	0.1127445	g	