



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Benfer, David W	<b>Contact Title</b>	Prod Compliance Engineer, Eng Proc Opt/LEANPD		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2018-03-29	<b>Contact Email</b>	dave.benfer@te.com				
<b>Contact Phone Number</b>	717-986-3725								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	5-5179010-1	<b>Amount</b>	994.57286988	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	0.8FH,R13H.5,040,08/Sn,TU	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-0117</b>	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
<b>Complex Article Description</b>	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	0.8 FH REC HSG 40P H13 BL=0.5				1.0	690.0	mg	
Material	2	LCP				1.0	690.0	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	207.0	mg	
Substance	3	1,4-Benzenedicarboxylic acid, polymer with [1,1-biphenyl]-4,4-diol, 4-hydroxybenzoic acid, 6-hydroxy-2-naphthalenecarboxylic acid and N-(4-hydroxyphenyl)acetamide	Supplier	147310-94-9	69.7	1.0	480.93	mg	
Substance	3	Octadecanoic acid, 1,1-[2,2-bis[[[1-oxooctadecyl]oxy]methyl]-1,3-propanediyl] ester	Supplier	115-83-3	0.3	1.0	2.07	mg	
Sub-Item	1	FH 0.8 9H,13H REC CONT AUFLASH-MATTE TIN				40.0	7.61432175	mg	
Material	2	Tin Plate				40.0	0.113223	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	40.0	2.2645E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	40.0	0.11292	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	40.0	7.92561E-5	mg	
Material	2	Nickel Plate				40.0	0.498	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	40.0	9.96E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	40.0	4.98E-4	mg	

Substance	3	Nickel	Nickel	7440-02-0	99.7	40.0	0.49651	mg	
Material	2	Gold Plate				40.0	0.00309875	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	40.0	0.00308945	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	40.0	1.0E-5	mg	
Material	2	Beryllium Copper				40.0	7.0	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	40.0	7.0E-5	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	40.0	0.0014	mg	
Substance	3	Iron	Supplier	7439-89-6	0.2	40.0	0.014	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.2	40.0	0.014	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.5	40.0	0.035	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.6	40.0	0.042	mg	
Substance	3	Copper	Supplier	7440-50-8	98.1535	40.0	6.87074	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	40.0	7.0E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	40.0	7.0E-4	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.2	40.0	0.014	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	40.0	3.5E-4	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	40.0	3.5E-5	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	40.0	0.0035	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	40.0	0.0035	mg	