



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Penica, John R	Contact Title	Sr Mgr Engineering, IND Central Eng		
Company Unique ID	TE Connectivity	Response Date	2018-03-26	Contact Email	jrpenica@te.com				
Contact Phone Number	+1-717-592-3266								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5-104549-7	Amount	2.77475538	Version	-	Identity			
Manufacturer Item Name	50 SYS50 S/M HDR DRST SHRDSN	Weight Uom	g	Mfr Site		Authority			
Date		UOM	Each						
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	SYSTEM 50 SFMNT HLDWN PLTD SN				3.0	0.02468129	g	
Material	2	Beryllium Copper				3.0	0.0238815	g	
Substance	3	Beryllium	Supplier	7440-41-7	2.0	3.0	4.7763E-4	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	3.0	2.38815E-6	g	
Substance	3	Manganese	Supplier	7439-96-5	0.02	3.0	4.7763E-6	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.2	3.0	4.7763E-5	g	
Substance	3	Silicon	Supplier	7440-21-3	0.2	3.0	4.7763E-5	g	
Substance	3	Iron	Supplier	7439-89-6	0.4	3.0	9.5526E-5	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	3.0	2.38815E-6	g	
Substance	3	Aluminum	Supplier	7429-90-5	0.2	3.0	4.7763E-5	g	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	3.0	2.38815E-7	g	
Substance	3	Copper	Supplier	7440-50-8	96.6535	3.0	0.02308231	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	3.0	2.38815E-5	g	
Substance	3	Nickel	Nickel	7440-02-0	0.2	3.0	4.7763E-5	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	3.0	1.194075E-6	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	3.0	1.194075E-7	g	
Material	2	Tin Plate				3.0	5.3742E-4	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	3.0	1.074836E-6	g	
Substance	3	Tin	Supplier	7440-31-5	99.73	3.0	5.3597E-4	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	3.0	3.761926E-7	g	
Material	2	Nickel Plate				3.0	2.6237E-4	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	3.0	5.2474E-7	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	3.0	2.6237E-7	g	

Substance	3	Nickel	Nickel	7440-02-0	99.7	3.0	2.6158E-4	g	
Sub-Item	1	50 SYSTEM 50 SURFMNT HDR HSG				1.0	1.525	g	
Material	2	LCP-GF35				1.0	1.525	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	2.0	1.0	0.0305	g	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	34.3	1.0	0.523075	g	
Substance	3	1,3-Benzenedicarboxylic acid, polymer with 1,4-benzenedicarboxylic acid, [1,1-biphenyl]-4,4-diol and 4-hydroxybenzoic acid	Supplier	60088-52-0	62.7	1.0	0.956175	g	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	0.01525	g	
Sub-Item	1	SYSTEM 50 POST PLTD 30 DPLX SN				50.0	0.02351423	g	
Material	2	Tin Plate				50.0	7.46E-5	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	50.0	1.492E-7	g	
Substance	3	Tin	Supplier	7440-31-5	99.73	50.0	7.439858E-5	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	50.0	5.222E-8	g	
Material	2	Gold Plate				50.0	6.02E-5	g	
Substance	3	Gold	Supplier	7440-57-5	99.7	50.0	6.00194E-5	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	50.0	1.806E-7	g	
Material	2	Nickel Plate				50.0	1.37E-4	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	50.0	2.74E-7	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	50.0	1.37E-7	g	
Substance	3	Nickel	Nickel	7440-02-0	99.7	50.0	1.3659E-4	g	
Material	2	Brass				50.0	0.02324	g	
Substance	3	Tin	Supplier	7440-31-5	0.1	50.0	2.324E-5	g	
Substance	3	Copper	Supplier	7440-50-8	64.0	50.0	0.0148736	g	
Substance	3	Iron	Supplier	7439-89-6	0.05	50.0	1.162E-5	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	50.0	2.324E-7	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	50.0	2.324E-6	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	50.0	2.324E-5	g	
Substance	3	Manganese	Supplier	7439-96-5	0.1	50.0	2.324E-5	g	
Substance	3	Zinc	Supplier	7440-66-6	35.2085	50.0	0.00818246	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	50.0	2.324E-6	g	
Substance	3	Chromium	Supplier	7440-47-3	0.01	50.0	2.324E-6	g	
Substance	3	Aluminum	Supplier	7429-90-5	0.05	50.0	1.162E-5	g	
Substance	3	Nickel	Nickel	7440-02-0	0.3	50.0	6.972E-5	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	50.0	2.324E-6	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	50.0	1.162E-7	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	50.0	1.162E-5	g	
Material	2	Gold Flash				50.0	2.43024E-6	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	50.0	1.0E-8	g	
Substance	3	Gold	Supplier	7440-57-5	99.7	50.0	2.422949E-6	g	