



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	TE Product Compliance	Contact Title	-		
Company Unique ID	TE Connectivity	Response Date	2018-12-13	Contact Email	productcompliance@te.com				
Contact Phone Number	+001-800-522-6752								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5177983-1	Amount	0.45484	Version	-	Identity			
Manufacturer Item Name	0.8FH,R05H.5,0 40,08/Sn,TU	Weight Uom	g	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	0.8 FH BTB CONT AS PLATED, LF				40.0	0.003121	g	
Material	2	Beryllium Copper				40.0	0.0030	g	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	40.0	3.0E-8	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	40.0	1.5E-7	g	
Substance	3	Cobalt	Supplier	7440-48-4	2.5	40.0	7.5E-5	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	40.0	3.0E-7	g	
Substance	3	Copper	Supplier	7440-50-8	94.5185	40.0	0.00283556	g	
Substance	3	Manganese	Supplier	7439-96-5	0.01	40.0	3.0E-7	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.4	40.0	1.2E-5	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	40.0	1.5E-8	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	40.0	1.5E-6	g	
Substance	3	Nickel	Nickel	7440-02-0	2.5	40.0	7.5E-5	g	
Substance	3	Cadmium	Cadmium/Cad mium Compounds	7440-43-9	0.0050	40.0	1.5E-7	g	
Material	2	Tin Plate				40.0	1.9E-5	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2- 1212	0.2	40.0	3.8E-8	g	
Substance	3	Tin	Supplier	7440-31-5	99.73	40.0	1.89487E-5	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	40.0	1.33E-8	g	
Material	2	Nickel Plate				40.0	1.0E-4	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2- 1212	0.2	40.0	2.0E-7	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	40.0	1.0E-7	g	
Substance	3	Nickel	Nickel	7440-02-0	99.7	40.0	9.97E-5	g	
Material	2	Gold Plate				40.0	2.0E-6	g	
Substance	3	Gold	Supplier	7440-57-5	99.7	40.0	1.994E-6	g	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	40.0	1.0E-8	g	
Sub-Item	1	0.8MM FH BTB REC HSG 40P,5H,0.5BL				1.0	0.33	g	
Material	2	LCP				1.0	0.33	g	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	0.099	g	
Substance	3	1,4-Benzenedicarboxylic acid, polymer with [1,1-biphenyl]-4,4-diol, 4-hydroxybenzoic acid, 6-hydroxy-2-naphthalenecarboxylic acid and N-(4-hydroxyphenyl)acetamide	Supplier	147310-94-9	69.7	1.0	0.23001	g	
Substance	3	Octadecanoic acid, 1,1-[2,2-bis[[1-(1-oxooctadecyl)oxy]methyl]-1,3-propanediyl] ester	Supplier	115-83-3	0.3	1.0	9.9E-4	g	