



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																	
Supplier Information																										
Company Name	TE Connectivity	Request Document ID		Contact Name	Penica, John R	Contact Title	Sr Mgr Engineering, IND Central Eng																			
Company Unique ID	TE Connectivity	Response Date	2018-03-23	Contact Email	jrpenica@te.com																					
Contact Phone Number	+1-717-592-3266																									
Legal Statement																										
Supplier Acceptance	true																									
Legal Statement																										
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																										
Product																										
Manufacturer Item number	5-104666-1	Amount	1.3275536	Version	-	Identity																				
Manufacturer Item Name	20 SYSTEM 50 HDR DRST SHRD SN	Weight Uom	g	Mfr Site		Authority																				
Date		UOM	Each																							
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions																									
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																									
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed																									
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed																									
Product Disclosure																										
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																	
Sub-Item	1	20 SYSTEM 50 HDR HSG DR LATCH				1.0	0.857269	g																		
Material	2	LCP-GF35				1.0	0.857269	g																		
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	2.0	1.0	0.01714538	g																		
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	34.3	1.0	0.29404327	g																		
Substance	3	1,3-Benzenedicarb oxylic acid, polymer with 1,4-benzenedicarb oxylic acid, [1,1-biphenyl]-4,4-diol and 4-hydroxybenzoi c acid	Supplier	60088-52-0	62.7	1.0	0.53750766	g																		
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	0.00857269	g																		
Sub-Item	1	SYSTEM 50 POST PLTD 30 DPLX SN				20.0	0.02351423	g																		
Material	2	Brass				20.0	0.02324	g																		
Substance	3	Tin	Supplier	7440-31-5	0.1	20.0	2.324E-5	g																		
Substance	3	Copper	Supplier	7440-50-8	64.0	20.0	0.0148736	g																		
Substance	3	Iron	Supplier	7439-89-6	0.05	20.0	1.162E-5	g																		
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	20.0	2.324E-7	g																		
Substance	3	Arsenic	Supplier	7440-38-2	0.01	20.0	2.324E-6	g																		
Substance	3	Cobalt	Supplier	7440-48-4	0.1	20.0	2.324E-5	g																		
Substance	3	Manganese	Supplier	7439-96-5	0.1	20.0	2.324E-5	g																		
Substance	3	Zinc	Supplier	7440-66-6	35.2085	20.0	0.00818246	g																		
Substance	3	Antimony	Supplier	7440-36-0	0.01	20.0	2.324E-6	g																		
Substance	3	Chromium	Supplier	7440-47-3	0.01	20.0	2.324E-6	g																		
Substance	3	Aluminum	Supplier	7429-90-5	0.05	20.0	1.162E-5	g																		
Substance	3	Nickel	Nickel	7440-02-0	0.3	20.0	6.972E-5	g																		
Substance	3	Cadmium	Cadmium/Cad mium Compounds	7440-43-9	0.01	20.0	2.324E-6	g																		

Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	20.0	1.162E-7	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	20.0	1.162E-5	g	
Material	2	Tin Plate				20.0	7.46E-5	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	20.0	1.492E-7	g	
Substance	3	Tin	Supplier	7440-31-5	99.73	20.0	7.439858E-5	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	20.0	5.222E-8	g	
Material	2	Gold Plate				20.0	6.02E-5	g	
Substance	3	Gold	Supplier	7440-57-5	99.7	20.0	6.00194E-5	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	20.0	1.806E-7	g	
Material	2	Gold Flash				20.0	2.43024E-6	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	20.0	1.0E-8	g	
Substance	3	Gold	Supplier	7440-57-5	99.7	20.0	2.422949E-6	g	
Material	2	Nickel Plate				20.0	1.37E-4	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	20.0	2.74E-7	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	20.0	1.37E-7	g	
Substance	3	Nickel	Nickel	7440-02-0	99.7	20.0	1.3659E-4	g	