



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Penica, John R	Contact Title	Sr Mgr Engineering, IND Central Eng																											
Company Unique ID	TE Connectivity	Response Date	2017-10-16	Contact Email	jrpenica@te.com																													
Contact Phone Number		+1-717-592-3266																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	51864-2	Amount	0.91131148	Version	-	Identity																												
Manufacturer Item Name	TERMINAL,PID G R 16-14 10	Weight Uom	g	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH																																	
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	BODY,RING 16-14 10				1.0	0.58457148	g																										
Material	2	Copper				1.0	0.578327	g																										
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	2.8916E-4	g																										
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	5.78327E-6	g																										
Substance	3	Copper	Supplier	7440-50-8	99.7575	1.0	0.57692456	g																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	5.78327E-6	g																										
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	1.0	2.891635E-5	g																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	5.78327E-5	g																										
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	1.1567E-4	g																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	5.7833E-4	g																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	2.8916E-4	g																										
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	2.891635E-6	g																										
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	2.891635E-5	g																										
Material	2	Tin Plate				1.0	0.00624448	g																										
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	0.00622762	g																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	1.248895E-5	g																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	4.371134E-6	g																										
Sub-Item	1	SLEEVE ASSEMBLY 16-14				1.0	0.32674	g																										
Material	2	Copper				1.0	0.302	g																										
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	1.51E-4	g																										
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	3.02E-6	g																										
Substance	3	Copper	Supplier	7440-50-8	99.7575	1.0	0.30126765	g																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	3.02E-6	g																										
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	1.0	1.51E-5	g																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	3.02E-5	g																										
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	6.04E-5	g																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	3.02E-4	g																										

Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	1.51E-4	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	1.51E-6	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	1.51E-5	g	
Material	2	PA66				1.0	0.0193452	g	
Substance	3	Phosphoric acid	Supplier	7664-38-2	0.075	1.0	1.45089E-5	g	
Substance	3	Acetic acid	Supplier	64-19-7	0.015	1.0	2.90178E-6	g	
Substance	3	Polyamide 66 - ISO 1043-1 Term PA66	Supplier	1043-1-PA66	89.39	1.0	0.01729267	g	
Substance	3	Acetic acid, copper(2) salt (2:1)	Supplier	142-71-2	0.02	1.0	3.86904E-6	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	10.0	1.0	0.00193452	g	
Substance	3	Potassium bromide	Supplier	7758-02-3	0.5	1.0	9.6726E-5	g	
Material	2	COLORANT				1.0	3.948E-4	g	
Substance	3	3H-Naphtho[1,2,3-de]quinoline-2,7-dione, 3-methyl-6-[(4-methylphenyl)amino]-	Supplier	81-39-0	0.1	1.0	3.948E-7	g	
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	0.323	1.0	1.275204E-6	g	
Substance	3	Naphthalene	Supplier	91-20-3	0.0017	1.0	1.0E-8	g	
Substance	3	Carbon black	Supplier	1333-86-4	0.0010	1.0	1.0E-8	g	
Substance	3	Copper, [29H,31H-phthalocyaninato(2-)-.kappa.N29,.kappa.N30,.kappa.N31,.kappa.N32]-, (SP-4-1)-	Supplier	147-14-8	0.418	1.0	1.650264E-6	g	
Substance	3	Octadecanamide, N,N-1,2-ethanediylbis-	Supplier	110-30-5	0.0090	1.0	3.5532E-8	g	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	98.9773	1.0	3.9076E-4	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.17	1.0	6.7116E-7	g	
Material	2	Tin Plate				1.0	0.0050	g	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	0.0049865	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	1.0E-5	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	3.5E-6	g	