



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Penica, John R	Contact Title	Sr Mgr Engineering, IND Central Eng		
Company Unique ID	TE Connectivity	Response Date	2018-04-03	Contact Email	jrpenica@te.com				
Contact Phone Number	+1-717-592-3266								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	52042-2	Amount	6.132721	Version	-	Identity			
Manufacturer Item Name	TERMINAL,R PG 6 8	Weight Uom	g	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	TERMINAL BRAZED RING 6 8				1.0	4.929721	g	
Material	2	Copper				1.0	4.8678	g	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	0.0024339	g	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	4.8678E-5	g	
Substance	3	Copper	Supplier	7440-50-8	99.7575	1.0	4.85599559	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	4.8678E-5	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	1.0	2.4339E-4	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	4.8678E-4	g	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	9.7356E-4	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.0048678	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.0024339	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	2.4339E-5	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	2.4339E-4	g	
Material	2	Tin Plate				1.0	0.03153	g	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	0.03144487	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	6.306E-5	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	2.2071E-5	g	
Material	2	Brazing Filler				1.0	0.030391	g	
Substance	3	Phosphorus	Supplier	7723-14-0	6.7	1.0	0.0020362	g	
Substance	3	Copper	Supplier	7440-50-8	87.05	1.0	0.02645537	g	
Substance	3	Silver	Supplier	7440-22-4	6.25	1.0	0.00189944	g	
Sub-Item	1	SLEEVE COLD FORMED PVC PG 6				1.0	1.203	g	
Material	2	COLORANT				1.0	0.0060	g	
Substance	3	Rosin	Supplier	8050-09-7	0.0090	1.0	5.4E-7	g	
Substance	3	Aluminum oxide (Al2O3)	Supplier	1344-28-1	0.5	1.0	3.0E-5	g	

Substance	3	8-Oxa-3,5-dithia-4-stannatetradecanoic acid, 10-ethyl-4-[[2-(2-ethylhexyl)oxy]-2-oxoethyl]thio]-4-methyl-7-oxo-, 2-ethylhexyl ester	Supplier	57583-34-3	0.8	1.0	4.8E-5	g	
Substance	3	8-Oxa-3,5-dithia-4-stannatetradecanoic acid, 10-ethyl-4,4-dimethyl-7-oxo-, 2-ethylhexyl ester	Supplier	57583-35-4	0.8	1.0	4.8E-5	g	
Substance	3	Octadecanoic acid, zinc salt (2:1)	Supplier	557-05-1	0.2	1.0	1.2E-5	g	
Substance	3	Ethene, chloro-, homopolymer	Supplier	9002-86-2	70.0	1.0	0.0042	g	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	6.0E-5	g	
Substance	3	Titanium oxide (TiO2)	Supplier	13463-67-7	11.0	1.0	6.6E-4	g	
Substance	3	Copper, [29H,31H-phthalocyaninato(2-)-.kappa.N29,.kappa.N30,.kappa.N31,.kappa.N32]-, (SP-4-1)-	Supplier	147-14-8	6.0	1.0	3.6E-4	g	
Substance	3	2-Naphthalenecarboxylic acid, 4-[2-(5-chloro-4-methyl-2-sulphophenyl)diazenyl]-3-hydroxy-, calcium salt (1:1)	Supplier	7023-61-2	0.3	1.0	1.8E-5	g	
Substance	3	Silica	Supplier	7631-86-9	0.5	1.0	3.0E-5	g	
Substance	3	Glycerol	Supplier	56-81-5	0.05	1.0	3.0E-6	g	
Substance	3	Ethene, chloro-	Supplier	75-01-4	3.0E-4	1.0	1.8E-8	g	
Substance	3	Limestone	Supplier	1317-65-3	1.0	1.0	6.0E-5	g	
Substance	3	Zeolites	Supplier	1318-02-1	1.0	1.0	6.0E-5	g	
Substance	3	Aluminate (Al(OH)63-), (OC-6-11)-, magnesium carbonate hydroxide (2:6:1:4)	Supplier	11097-59-9	0.7	1.0	4.2E-5	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	5.1357	1.0	3.0814E-4	g	
Substance	3	Octadecanoic acid, calcium salt (2:1)	Supplier	1592-23-0	1.0	1.0	6.0E-5	g	
Substance	3	Quartz (SiO2)	Supplier	14808-60-7	0.0050	1.0	3.0E-7	g	
Material	2	PVC				1.0	1.197	g	
Substance	3	Ethene, chloro-	Supplier	75-01-4	4.0E-4	1.0	4.788E-6	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	7.5	1.0	0.089775	g	
Substance	3	Ethene, chloro-, homopolymer	Supplier	9002-86-2	87.9961	1.0	1.05331332	g	
Substance	3	8-Oxa-3,5-dithia-4-stannatetradecanoic acid, 10-ethyl-4,4-dimethyl-7-oxo-, 2-ethylhexyl ester	Supplier	57583-35-4	1.5	1.0	0.017955	g	
Substance	3	Octadecanoic acid, calcium salt (2:1)	Supplier	1592-23-0	0.5	1.0	0.005985	g	
Substance	3	Calcium hydroxide (Ca(OH)2)	Supplier	1305-62-0	0.0035	1.0	4.1895E-5	g	

Substance	3	8-Oxa-3,5-dithia-4-stannatetradecanoic acid, 10-ethyl-4-[[2-[(2-ethylhexyl)oxy]-2-oxoethyl]thio]-4-methyl-7-oxo-, 2-ethylhexyl ester	Supplier	57583-34-3	0.5	1.0	0.005985	g	
Substance	3	Limestone	Supplier	1317-65-3	2.0	1.0	0.02394	g	