



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer David W	Contact Title	Product Compliance Engineer for DND		
Company Unique ID	TE Connectivity	Response Date	2017-09-05	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5177984-3	Amount	714.294752	Version	-	Identity			
Manufacturer Item Name	0.8FH,P05H.5,080,08/Sn,TU	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	0.8MM FH PLUG HSG, H=5MM 80P				1.0	520.0	mg	
Material	2	LCP				1.0	520.0	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	156.0	mg	
Substance	3	1,4-Benzenedicarb oxylic acid, polymer with [1,1-biphenyl]-4,4-diol, 4-hydroxybenzoic acid, 6-hydroxy-2-naphthalenecarboxylic acid and N-(4-hydroxyphenyl)acetamide	Supplier	147310-94-9	69.7	1.0	362.44	mg	
Substance	3	Octadecanoic acid, 1,1-[2,2-bis[[[1-oxooctadecyl]oxy]methyl]-1,3-propanediyl] ester	Supplier	115-83-3	0.3	1.0	1.56	mg	
Sub-Item	1	.8FH,P05H,CN T,08Au/Sn,RE-REEL				80.0	2.4286844	mg	
Material	2	Gold Plate				80.0	0.002702	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	80.0	0.00269389	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	80.0	1.0E-5	mg	
Material	2	Nickel Plate				80.0	0.0393024	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	80.0	7.86048E-5	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	80.0	3.93024E-5	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	80.0	0.03918449	mg	
Material	2	Tin Plate				80.0	0.01168	mg	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	80.0	2.336E-5	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	80.0	0.01164846	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	80.0	1.0E-5	mg	
Material	2	Brass				80.0	2.375	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	80.0	2.375E-5	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	80.0	0.66553	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	80.0	0.0011875	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	80.0	2.375E-4	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	80.0	0.0011875	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	80.0	0.002375	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	80.0	1.69813	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	80.0	2.375E-5	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	80.0	2.375E-4	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	80.0	1.1875E-5	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	80.0	0.00475	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	80.0	1.1875E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	80.0	0.0011875	mg	