



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	TE PRODUCT COMPLIANCE	Contact Title			
Company Unique ID	TE Connectivity	Response Date	2018-08-22	Contact Email	productcompliance@te.com				
Contact Phone Number	+001-800-522-6752								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	530153-2	Amount	0.3765	Version	-	Identity			
Manufacturer Item Name	TDM SPRING SHUNT ASSY 2 POS	Weight Uom	g	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	TDM SPRING, HOUSING, SHUNT				0.25	0.33	g	
Material	2	PBT				0.25	0.3168	g	
Substance	3	Benzenepropionic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	0.25	6.336E-4	g	
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	5.0	0.25	0.01584	g	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.1	0.25	3.168E-4	g	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	8.0	0.25	0.025344	g	
Substance	3	7-Oxabicyclo[4.1.0]heptane-3-carboxylic acid, 7-oxabicyclo[4.1.0]hept-3-ylmethyl ester	Supplier	2386-87-0	0.1	0.25	3.168E-4	g	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	0.25	0.001584	g	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	0.1	0.25	3.168E-4	g	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.5	0.25	0.001584	g	

Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	156042-31-8	30.0	0.25	0.09504	g	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	111211-39-3	5.0	0.25	0.01584	g	
Substance	3	Acetic acid ethenyl ester, polymer with ethene	Supplier	24937-78-8	2.0	0.25	0.006336	g	
Substance	3	Phosphorous acid, decyl diphenyl ester	Supplier	3287-06-7	0.1	0.25	3.168E-4	g	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	48.4	0.25	0.1533312	g	
Material	2	COLORANT				0.25	0.0132	g	
Substance	3	Carbon black	Supplier	1333-86-4	20.0	0.25	0.00264	g	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	78.4	0.25	0.0103488	g	
Substance	3	Octadecanamide, N,N-1,2-ethanediyldis-	Supplier	110-30-5	1.6	0.25	2.112E-4	g	
Sub-Item	1	TDM SPRING SHUNT CONTACT STRIP				2.0	0.147	g	
Material	2	Phos Bronze				2.0	0.14553	g	
Substance	3	Manganese	Supplier	7439-96-5	0.02	2.0	2.9106E-5	g	
Substance	3	Copper	Supplier	7440-50-8	93.1485	2.0	0.13555901	g	
Substance	3	Zinc	Supplier	7440-66-6	0.3	2.0	4.3659E-4	g	
Substance	3	Chromium	Supplier	7440-47-3	0.01	2.0	1.4553E-5	g	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	2.0	5.0935E-4	g	
Substance	3	Iron	Supplier	7439-89-6	0.1	2.0	1.4553E-4	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	2.0	7.2765E-6	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	1.4553E-6	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	1.4553E-4	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	1.4553E-5	g	
Substance	3	Tin	Supplier	7440-31-5	5.8	2.0	0.00844074	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	2.0	7.2765E-6	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	7.2765E-7	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	2.0	7.2765E-5	g	
Substance	3	Nickel	Nickel	7440-02-0	0.1	2.0	1.4553E-4	g	
Material	2	Nickel Plate				2.0	7.35E-4	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	7.35E-7	g	
Substance	3	Nickel	Nickel	7440-02-0	99.7	2.0	7.3279E-4	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.0	1.47E-6	g	
Material	2	INLay- GOLD				2.0	7.35E-4	g	
Substance	3	Nickel	Nickel	7440-02-0	0.01	2.0	7.35E-8	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	1.0E-8	g	
Substance	3	Platinum	Supplier	7440-06-4	7.0	2.0	5.145E-5	g	
Substance	3	Gold	Supplier	7440-57-5	66.4425	2.0	4.8835E-4	g	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	2.0	1.0E-8	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	7.35E-8	g	
Substance	3	Manganese	Supplier	7439-96-5	0.01	2.0	7.35E-8	g	
Substance	3	Silver	Supplier	7440-22-4	26.5	2.0	1.9477E-4	g	

Substance	3	Cobalt	Supplier	7440-48-4	0.01	2.0	7.35E-8	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	2.0	3.675E-8	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.01	2.0	7.35E-8	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	1.0E-8	g	