



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer		
Company Unique ID	TE Connectivity	Response Date	2017-09-26	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5188835-1	Amount	8018.3219392	Version	-	Identity			
Manufacturer Item Name	Z-PACK/B M-HDR 154P.	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	2MM H.M. 12PDNI, MALE CONTACT,				44.0	30.6643168	mg	
Material	2	Palladium-Nickel Plate				44.0	0.021598	mg	
Substance	3	Palladium	Supplier	7440-05-3	80.0	44.0	0.0172784	mg	
Substance	3	Nickel	Nickel	7440-02-0	20.0	44.0	0.0043196	mg	
Material	2	Tin Plate				44.0	0.0902773	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	44.0	1.8055E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	44.0	0.09003355	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	44.0	6.319411E-5	mg	
Material	2	Phos Bronze				44.0	30.25	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	44.0	28.6463	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	44.0	0.00605	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	44.0	0.003025	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	44.0	1.36125	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	44.0	0.0015125	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	44.0	0.03025	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	44.0	0.003025	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	44.0	3.025E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	44.0	0.09075	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	44.0	0.03025	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	44.0	0.03025	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	44.0	0.0015125	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	44.0	0.015125	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	44.0	0.03025	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	44.0	1.5125E-4	mg	
Material	2	Gold Plate				44.0	0.0124415	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	44.0	0.01240418	mg	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	44.0	3.73245E-5	mg	
Material	2	Nickel Plate				44.0	0.29	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	44.0	5.8E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	44.0	2.9E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	44.0	0.28913	mg	
Sub-Item	1	2MMHM,CNT, 12pd-ni, type B				110.0	28.6372	mg	
Material	2	Palladium-Nickel Plate				110.0	0.0171	mg	
Substance	3	Palladium	Supplier	7440-05-3	80.0	110.0	0.01368	mg	
Substance	3	Nickel	Nickel	7440-02-0	20.0	110.0	0.00342	mg	
Material	2	Tin Plate				110.0	0.0903	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	110.0	1.806E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	110.0	0.09005619	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	110.0	6.321E-5	mg	
Material	2	Phos Bronze				110.0	28.25	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	110.0	26.75233	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	110.0	0.00565	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	110.0	0.002825	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	110.0	1.27125	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	110.0	0.0014125	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	110.0	0.02825	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	110.0	0.002825	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	110.0	2.825E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	110.0	0.08475	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	110.0	0.02825	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	110.0	0.02825	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	110.0	0.0014125	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	110.0	0.014125	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	110.0	0.02825	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	110.0	1.4125E-4	mg	
Material	2	Gold Plate				110.0	0.0098	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	110.0	0.0097706	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	110.0	2.94E-5	mg	
Material	2	Nickel Plate				110.0	0.27	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	110.0	5.4E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	110.0	2.7E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	110.0	0.26919	mg	
Sub-Item	1	2MMHM,5R,H SG,TYPE B HDR,154P				1.0	3519.0	mg	
Material	2	PBT-GF20-FR(17)				1.0	3519.0	mg	
Substance	3	C.I. Pigment Yellow 119	Supplier	68187-51-9	1.0	1.0	35.19	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	18.0	1.0	633.42	mg	
Substance	3	C.I. Disperse Yellow 201	Supplier	80748-21-6	0.0020	1.0	0.07038	mg	

Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	1.0	7.038	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	1.0	1.0	35.19	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.5	1.0	17.595	mg	
Substance	3	Carbon black	Supplier	1333-86-4	0.1	1.0	3.519	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	48.498	1.0	1706.64462	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	879.75	mg	
Substance	3	Zinc sulfide (ZnS)	Supplier	1314-98-3	5.0	1.0	175.95	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	0.5	1.0	17.595	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.2	1.0	7.038	mg	