



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	JOHN PENICA	<b>Contact Title</b>	Sr. Mgr. Global PEC_INDUSTRIAL		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2017-05-09	<b>Contact Email</b>	jrpenica@tycoelectronics.com				
<b>Contact Phone Number</b>	717-592-3266								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	5435802-9	<b>Amount</b>	1.9123899	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	RIGHT ANGLE DIP SW 8 P SEALED	<b>Weight Uom</b>	g	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-0616</b>	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
<b>Complex Article Description</b>	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	LOWER CONTACT FORMED				9.0	0.0130082	g	
Material	2	Beryllium Copper				9.0	0.0125	g	
Substance	3	Copper	Supplier	7440-50-8	96.9485	9.0	0.01211856	g	
Substance	3	Manganese	Supplier	7439-96-5	0.02	9.0	2.5E-6	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	9.0	1.25E-6	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.6	9.0	7.5E-5	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	9.0	1.25E-6	g	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	9.0	1.25E-7	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	9.0	1.25E-5	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	9.0	1.25E-6	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	9.0	1.25E-5	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	9.0	6.25E-8	g	
Substance	3	Nickel	Nickel	7440-02-0	2.2	9.0	2.75E-4	g	
Material	2	Tin Plate				9.0	1.24E-4	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	9.0	2.48E-7	g	
Substance	3	Tin	Supplier	7440-31-5	99.73	9.0	1.2367E-4	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	9.0	8.68E-8	g	
Material	2	Gold Plate				9.0	3.2E-6	g	
Substance	3	Gold	Supplier	7440-57-5	99.7	9.0	3.1904E-6	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	9.0	1.0E-8	g	
Material	2	Nickel Plate				9.0	3.81E-4	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	9.0	7.62E-7	g	

Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	9.0	3.81E-7	g	
Substance	3	Nickel	Nickel	7440-02-0	99.7	9.0	3.7986E-4	g	
Sub-Item	1	Adhesive and Sealants				1.0	0.32250418	g	
Material	2	Plastic Coating - Sealant				1.0	0.32250418	g	
Substance	3	1,2-Benzenedicarboxylic acid, di-C9-11-branched alkyl esters, C10-rich	Phthalates (DINP, DIDP, DNOP)	68515-49-1	20.0	1.0	0.06450084	g	
Substance	3	Castor-oil	Supplier	8001-79-4	20.0	1.0	0.06450084	g	
Substance	3	CELLULOSE, ACETATE BUTYRATE	Supplier	9004-36-8	50.0	1.0	0.16125209	g	
Substance	3	Soybean oil, epoxidized	Supplier	8013-07-8	10.0	1.0	0.03225042	g	
Sub-Item	1	CASE, SIDE ACT DIP SW 8 POS				1.0	0.637621	g	
Material	2	PBT-I-GF30-FR(17)				1.0	0.637621	g	
Substance	3	Dolomite (CaMg(CO3)2)	Supplier	16389-88-1	0.5	1.0	0.00318811	g	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	35.0	1.0	0.22316735	g	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	1.0	0.00127524	g	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.2	1.0	0.00127524	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	1.0	0.01912863	g	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	2.0	1.0	0.01275242	g	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	1.0	1.0	0.00637621	g	
Substance	3	Chlorite-group minerals	Supplier	1318-59-8	0.5	1.0	0.00318811	g	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	0.00637621	g	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	36.6	1.0	0.23336929	g	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	1.0	0.00318811	g	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	18.0	1.0	0.11477178	g	
Substance	3	Quartz (SiO2)	Supplier	14808-60-7	0.5	1.0	0.00318811	g	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	1.0	1.0	0.00637621	g	
Sub-Item	1	CORE TYPE C MOLDED 8 POS				1.0	0.538	g	
Material	2	PBT-I-GF30-FR(17)				1.0	0.538	g	
Substance	3	Dolomite (CaMg(CO3)2)	Supplier	16389-88-1	0.5	1.0	0.00269	g	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	35.0	1.0	0.1883	g	

Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	1.0	0.001076	g	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.2	1.0	0.001076	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	1.0	0.01614	g	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	2.0	1.0	0.01076	g	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	1.0	1.0	0.00538	g	
Substance	3	Chlorite-group minerals	Supplier	1318-59-8	0.5	1.0	0.00269	g	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	0.00538	g	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	36.6	1.0	0.196908	g	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	1.0	0.00269	g	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	18.0	1.0	0.09684	g	
Substance	3	Quartz (SiO2)	Supplier	14808-60-7	0.5	1.0	0.00269	g	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	1.0	1.0	0.00538	g	
Sub-Item	1	UPPER SPRING CONTACT FORMED				9.0	0.01304788	g	
Material	2	Beryllium Copper				9.0	0.012537	g	
Substance	3	Copper	Supplier	7440-50-8	96.9485	9.0	0.01215443	g	
Substance	3	Manganese	Supplier	7439-96-5	0.02	9.0	2.5074E-6	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	9.0	1.2537E-6	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.6	9.0	7.5222E-5	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	9.0	1.2537E-6	g	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	9.0	1.2537E-7	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	9.0	1.2537E-5	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	9.0	1.2537E-6	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	9.0	1.2537E-5	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	9.0	6.2685E-8	g	
Substance	3	Nickel	Nickel	7440-02-0	2.2	9.0	2.7581E-4	g	
Material	2	Tin Plate				9.0	1.24E-4	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	9.0	2.48E-7	g	
Substance	3	Tin	Supplier	7440-31-5	99.73	9.0	1.2367E-4	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	9.0	8.68E-8	g	
Material	2	Gold Plate				9.0	6.88E-6	g	
Substance	3	Gold	Supplier	7440-57-5	99.7	9.0	6.85936E-6	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	9.0	2.064E-8	g	
Material	2	Nickel Plate				9.0	3.8E-4	g	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	9.0	7.6E-7	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	9.0	3.8E-7	g	
Substance	3	Nickel	Nickel	7440-02-0	99.7	9.0	3.7886E-4	g	
Sub-Item	1	CAM, SIDE ACT DIP SW				8.0	0.02247	g	
Material	2	PBT				8.0	0.02247	g	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	8.0	4.494E-5	g	
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	5.0	8.0	0.0011235	g	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.1	8.0	2.247E-5	g	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	8.0	8.0	0.0017976	g	
Substance	3	7-Oxabicyclo[4.1.0]heptane-3-carboxylic acid, 7-oxabicyclo[4.1.0]hept-3-ylmethyl ester	Supplier	2386-87-0	0.1	8.0	2.247E-5	g	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	8.0	1.1235E-4	g	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	0.1	8.0	2.247E-5	g	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.5	8.0	1.1235E-4	g	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	156042-31-8	30.0	8.0	0.006741	g	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	111211-39-3	5.0	8.0	0.0011235	g	
Substance	3	Acetic acid ethenyl ester, polymer with ethene	Supplier	24937-78-8	2.0	8.0	4.494E-4	g	
Substance	3	Phosphorous acid, decyl diphenyl ester	Supplier	3287-06-7	0.1	8.0	2.247E-5	g	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	48.4	8.0	0.01087548	g	