



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	TE Product Compliance	<b>Contact Title</b>	Prod Compliance Engineer, Eng Proc Opt/LEANPD		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2018-10-15	<b>Contact Email</b>	productcompliance@te.com				
<b>Contact Phone Number</b>	1-800-522-6752								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	5555165-1	<b>Amount</b>	2261.719686	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	M/J, LPF, R/A, 6P/6C, TIN, BUL	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-0117</b>	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
<b>Complex Article Description</b>	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	HSG, 6 POS, LPF, R/A, MOD JACK				1.0	1947.2	mg	
Material	2	PBT-GF20-FR(17)				1.0	1947.2	mg	
Substance	3	Benzenepropionic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	1.0	3.8944	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	486.8	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	5.0	1.0	97.36	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.5	1.0	9.736	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	0.5	1.0	9.736	mg	
Substance	3	Phosphoric acid, zinc salt (2:1)	Supplier	13598-37-3	0.3	1.0	5.8416	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.5	1.0	29.208	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	17.0	1.0	331.024	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.2	1.0	3.8944	mg	

Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	97.36	mg	
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	5.0	1.0	97.36	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	39.796	1.0	774.90771	mg	
Substance	3	Arsenic oxide (As2O3)	Arsenic oxide (As2O3)	1327-53-3	0.0020	1.0	0.038944	mg	
Substance	3	Lead oxide (lead monoxide)	Lead/Lead Compounds	1317-36-8	0.0020	1.0	0.038944	mg	
Sub-Item	1	TERM, LPF, R/A, TIN, MOD JACK, 6 POS				1.0	314.519686	mg	
Material	2	Nickel Plate				1.0	2.24	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00224	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.00448	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	2.23328	mg	
Material	2	Tin Plate				1.0	2.03	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.00406	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	2.02452	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	0.001421	mg	
Material	2	Gold Plate				1.0	0.069686	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	1.0	2.0906E-4	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	0.06947694	mg	
Material	2	Phos Bronze				1.0	310.18	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.31018	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.031018	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.2	1.0	0.62036	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	1.0	0.015509	mg	
Substance	3	Copper	Supplier	7440-50-8	90.0485	1.0	279.31244	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.062036	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	1.0	1.08563	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.0031018	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	0.31018	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.031018	mg	
Substance	3	Tin	Supplier	7440-31-5	9.0	1.0	27.9162	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	0.31018	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.0015509	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.015509	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.15509	mg	