



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer David W	Contact Title	Product Compliance Engineer for DND		
Company Unique ID	TE Connectivity	Response Date	2018-04-23	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5555166-1	Amount	2381.7876	Version	-	Identity			
Manufacturer Item Name	MJ,LPF,R/A,8P/8 C,PNL STOPS,KE	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	TERM, LPF, R/A, TIN, MOD JACK, 8 POS				1.0	390.7876	mg	
Material	2	Tin Plate				1.0	2.714	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.005428	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	2.70667	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	0.0018998	mg	
Material	2	Phos Bronze				1.0	385.2	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.3852	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.03852	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.2	1.0	0.7704	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	1.0	0.01926	mg	
Substance	3	Copper	Supplier	7440-50-8	90.0485	1.0	346.86682	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.07704	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	1.0	1.3482	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.003852	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	0.3852	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.03852	mg	
Substance	3	Tin	Supplier	7440-31-5	9.0	1.0	34.668	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	0.3852	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.001926	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.01926	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.1926	mg	
Material	2	Gold Plate				1.0	0.0878	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	1.0	2.634E-4	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	0.0875366	mg	
Material	2	Nickel Plate				1.0	2.7858	mg	

Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.0027858	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.0055716	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	2.77744	mg	
Sub-Item	1	HSG,8POS,LP F,R/A,MOD JACK				1.0	1991.0	mg	
Material	2	PBT-GF20-FR(17)				1.0	1991.0	mg	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	1.0	3.982	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	497.75	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	5.0	1.0	99.55	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.5	1.0	9.955	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	0.5	1.0	9.955	mg	
Substance	3	Phosphoric acid, zinc salt (2:1)	Supplier	13598-37-3	0.3	1.0	5.973	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.5	1.0	29.865	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	17.0	1.0	338.47	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.2	1.0	3.982	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	99.55	mg	
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	5.0	1.0	99.55	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	39.796	1.0	792.33836	mg	
Substance	3	Arsenic oxide (As2O3)	Arsenic oxide (As2O3)	1327-53-3	0.0020	1.0	0.03982	mg	
Substance	3	Lead oxide (lead monoxide)	Lead/Lead Compounds	1317-36-8	0.0020	1.0	0.03982	mg	