



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name		Contact Title	Prod Compliance Engineer		
Company Unique ID	TE Connectivity	Response Date	2018-10-22	Contact Email	productcompliance@te.com				
Contact Phone Number	+001-800-522-6752								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5406721-2	Amount	1415.9508	Version	-	Identity			
Manufacturer Item Name	MJ,RJ45,SM,TG RAY,13"REEL	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	BOARD LOCK,INVERT ED M/JK				2.0	39.085	mg	
Material	2	Tin Plate				2.0	1.404	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.0	0.002808	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	2.0	1.40021	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	2.0	9.828E-4	mg	
Material	2	Phos Bronze				2.0	37.0	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.037	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.0037	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.2	2.0	0.074	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	2.0	0.00185	mg	
Substance	3	Copper	Supplier	7440-50-8	90.0485	2.0	33.31795	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	2.0	0.0074	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	2.0	0.1295	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	3.7E-4	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	2.0	0.037	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	2.0	0.0037	mg	
Substance	3	Tin	Supplier	7440-31-5	9.0	2.0	3.33	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	2.0	0.037	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	1.85E-4	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	2.0	0.00185	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	2.0	0.0185	mg	
Material	2	Nickel Plate				2.0	0.681	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.0	0.001362	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	6.81E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	2.0	0.67896	mg	

Sub-Item	1	HSG,1X1,8PO S,SMT,M/JK,G RAY				1.0	1197.0	mg	
Material	2	PS-ST-GF30 FR(17)				1.0	1197.0	mg	
Substance	3	Benzene, ethenyl- homopolymer	Supplier	9003-53-6	48.95	1.0	585.9315	mg	
Substance	3	Benzene, ethenyl- polymer with 2- methyl-1,3- butadiene, hydrogenated	Supplier	68648-89-5	0.8	1.0	9.576	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	1.6	1.0	19.152	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	359.1	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2- 0217	9.65	1.0	115.5105	mg	
Substance	3	Benzene, 1,1- (1,2- ethanediy)bis[2,3,4,5,6- pentabromo-	Brominated Flame Retardants (other than PBBs or PBDEs)	84852-53-9	9.0	1.0	107.73	mg	
Sub-Item	1	TERMINAL,SM T,MOD JK,PLATED				8.0	17.5976	mg	
Material	2	Gold Plate				8.0	0.01	mg	
Substance	3	Gold	Supplier	7440-57-5	99.0	8.0	0.0099	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2- 1212	1.0	8.0	1.0E-4	mg	
Material	2	Tin Plate				8.0	0.0876	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2- 1212	0.2	8.0	1.752E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	8.0	0.08736348	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	8.0	6.132E-5	mg	
Material	2	Phos Bronze				8.0	17.5	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	8.0	0.0175	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	8.0	0.00175	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.2	8.0	0.035	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	8.0	8.75E-4	mg	
Substance	3	Copper	Supplier	7440-50-8	90.0485	8.0	15.75849	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	8.0	0.0035	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	8.0	0.06125	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	8.0	1.75E-4	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	8.0	0.0175	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	8.0	0.00175	mg	
Substance	3	Tin	Supplier	7440-31-5	9.0	8.0	1.575	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	8.0	0.0175	mg	
Substance	3	Mercury	Mercury/Mercu ry Compounds	7439-97-6	5.0E-4	8.0	8.75E-5	mg	
Substance	3	Cadmium	Cadmium/Cad mium Compounds	7440-43-9	0.0050	8.0	8.75E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	8.0	0.00875	mg	