



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Benfer David W	<b>Contact Title</b>	Product Compliance Engineer for DND		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2018-04-04	<b>Contact Email</b>	dave.benfer@te.com				
<b>Contact Phone Number</b>	717-986-3725								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	5536446-5	<b>Amount</b>	6887.943168	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	ASSEMBLY,RE CEPTACLE,EUR OCARD,T	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-0117</b>	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
<b>Complex Article Description</b>	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	CONTACT,RE CEPT,VERT,E UROCARD,SO LDER,LEAD				32.0	58.998224	mg	
Material	2	Phos Bronze				32.0	58.1	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	32.0	55.01983	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	32.0	0.01162	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	32.0	0.00581	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	32.0	2.6145	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	32.0	0.002905	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	32.0	0.0581	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	32.0	0.00581	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	32.0	5.81E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	32.0	0.1743	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	32.0	0.0581	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	32.0	0.0581	mg	
Substance	3	Cadmium	Cadmium/Cad mium Compounds	7440-43-9	0.0050	32.0	0.002905	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	32.0	0.02905	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	32.0	0.0581	mg	
Substance	3	Mercury	Mercury/Mercu ry Compounds	7439-97-6	5.0E-4	32.0	2.905E-4	mg	
Material	2	Tin Plate				32.0	0.193857	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2- 1212	0.2	32.0	3.8771E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	32.0	0.19333	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	32.0	1.357E-4	mg	
Material	2	Nickel Plate				32.0	0.693708	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2- 1212	0.2	32.0	0.00138742	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	32.0	6.9371E-4	mg	

Substance	3	Nickel	Nickel	7440-02-0	99.7	32.0	0.69163	mg	
Material	2	Gold Plate				32.0	0.001463	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	32.0	0.00145861	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	32.0	1.0E-5	mg	
Material	2	Palladium-Nickel Plate				32.0	0.009196	mg	
Substance	3	Palladium	Supplier	7440-05-3	80.0	32.0	0.0073568	mg	
Substance	3	Nickel	Nickel	7440-02-0	20.0	32.0	0.0018392	mg	
Sub-Item	1	EUROCARD 32 POS TTR B HSG				1.0	5000.0	mg	
Material	2	PBT-GF30-FR(17)				1.0	5000.0	mg	
Substance	3	Silica	Supplier	7631-86-9	0.0050	1.0	0.25	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.2	1.0	10.0	mg	
Substance	3	Iron oxide (Fe2O3)	Supplier	1309-37-1	0.0040	1.0	0.2	mg	
Substance	3	C.I. Pigment Green 50	Supplier	68186-85-6	0.02	1.0	1.0	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	2.0	1.0	100.0	mg	
Substance	3	1,3-Propanediol, 2-amino-2-(hydroxymethyl)-	Supplier	77-86-1	0.5	1.0	25.0	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	1.0	1.0	50.0	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	1.0	1.0	50.0	mg	
Substance	3	Zinc sulfide (ZnS)	Supplier	1314-98-3	4.0	1.0	200.0	mg	
Substance	3	C.I. Pigment Blue 28	Supplier	1345-16-0	0.02	1.0	1.0	mg	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.1	1.0	5.0	mg	
Substance	3	Quartz (SiO2)	Supplier	14808-60-7	0.0030	1.0	0.15	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	35.0	1.0	1750.0	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	5.0	1.0	250.0	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	32.943	1.0	1647.15	mg	
Substance	3	Chlorite-group minerals	Supplier	1318-59-8	0.1	1.0	5.0	mg	
Substance	3	Dolomite (CaMg(CO3)2)	Supplier	16389-88-1	0.05	1.0	2.5	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	18.0	1.0	900.0	mg	
Substance	3	Carbon black	Supplier	1333-86-4	0.05	1.0	2.5	mg	
Substance	3	Arsenic oxide (As2O3)	Arsenic oxide (As2O3)	1327-53-3	0.0020	1.0	0.1	mg	
Substance	3	Lead oxide (lead monoxide)	Lead/Lead Compounds	1317-36-8	0.0030	1.0	0.15	mg	