



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer David W	Contact Title	Product Compliance Engineer for DND		
Company Unique ID	TE Connectivity	Response Date	2018-04-06	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5747846-3	Amount	12432.35146304	Version	-	Identity			
Manufacturer Item Name	25 MSFL RCPT RA 318 (IN,FM,BL)	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	25 MSFL FACE COVER				1.0	537.0	mg	
Material	2	PA46-GF30 FR(17)				1.0	537.0	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	19.0	1.0	102.03	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	7.0	1.0	37.59	mg	
Substance	3	Carbon black	Supplier	1333-86-4	0.9	1.0	4.833	mg	
Substance	3	Aluminate (Al(OH)63-), (OC-6-11)-, magnesium carbonate hydroxide (2:6:1:4)	Supplier	11097-59-9	0.9	1.0	4.833	mg	
Substance	3	Polyamide 46 - ISO 1043-1 Term PA46	Supplier	1043-1-PA46	32.2	1.0	172.914	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	161.1	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0217	10.0	1.0	53.7	mg	
Sub-Item	1	SCKT CNT PLTD 20DF 318 LR FLAU				12.0	92.17379367	mg	
Material	2	Nickel Plate				12.0	1.62	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	12.0	0.00324	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	12.0	0.00162	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	12.0	1.61514	mg	
Material	2	Gold Plate				12.0	0.0410967	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	12.0	0.04097341	mg	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	12.0	1.2329E-4	mg	
Material	2	Gold Flash				12.0	0.00269697	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	12.0	1.0E-5	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	12.0	0.00268888	mg	
Material	2	Tin Plate				12.0	0.31	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	12.0	6.2E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	12.0	0.30916	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	12.0	2.17E-4	mg	
Material	2	Phos Bronze				12.0	90.2	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	12.0	85.41805	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	12.0	0.01804	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	12.0	0.00902	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	12.0	4.059	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	12.0	0.00451	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	12.0	0.0902	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	12.0	0.00902	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	12.0	9.02E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	12.0	0.2706	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	12.0	0.0902	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	12.0	0.0902	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	12.0	0.00451	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	12.0	0.0451	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	12.0	0.0902	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	12.0	4.51E-4	mg	
Sub-Item	1	25 MSFL RCPT RA 318 HSG				1.0	5063.4	mg	
Material	2	PA66-GF25				1.0	5063.4	mg	
Substance	3	Benzenamine, reaction products with aniline hydrochloride and nitrobenzene	Supplier	101357-15-7	4.0	1.0	202.536	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediy)]imino-1,6-hexanediy]	Supplier	32131-17-2	61.5	1.0	3113.991	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0217	3.5	1.0	177.219	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	6.0	1.0	303.804	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	1265.85	mg	
Sub-Item	1	SCKT CNT PLTD 20DF 318 UR FLAU				13.0	114.368503	mg	
Material	2	Nickel Plate				13.0	1.9	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	13.0	0.0038	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	13.0	0.0019	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	13.0	1.8943	mg	
Material	2	Gold Plate				13.0	1.4	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	13.0	1.3958	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	13.0	0.0042	mg	
Material	2	Gold Flash				13.0	0.068503	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	13.0	2.0551E-4	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	13.0	0.06829749	mg	
Material	2	Tin Plate				13.0	3.1	mg	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	13.0	0.0062	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	13.0	3.09163	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	13.0	0.00217	mg	
Material	2	Phos Bronze				13.0	107.9	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	13.0	102.17968	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	13.0	0.02158	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	13.0	0.01079	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	13.0	4.8555	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	13.0	0.005395	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	13.0	0.1079	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	13.0	0.01079	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	13.0	0.001079	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	13.0	0.3237	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	13.0	0.1079	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	13.0	0.1079	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	13.0	0.005395	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	13.0	0.05395	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	13.0	0.1079	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	13.0	5.395E-4	mg	
Sub-Item	1	EYELET, FORMED, TIN				2.0	154.74	mg	
Material	2	Brass				2.0	148.0	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	2.0	0.00148	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	2.0	41.4733	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	2.0	0.074	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.0148	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	2.0	0.074	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.148	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	2.0	105.82	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.00148	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.0148	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	7.4E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	2.0	0.296	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	2.0	0.0074	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	2.0	0.074	mg	
Material	2	Tin Plate				2.0	3.03	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	2.0	0.002121	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.0	0.00606	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	2.0	3.02182	mg	
Material	2	Copper Plate				2.0	3.71	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	0.00371	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	2.0	3.70629	mg	
Sub-Item	1	BOARDLOCK, STRIP, PLATED				2.0	131.89	mg	
Material	2	Brass				2.0	127.7	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	2.0	0.001277	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	2.0	35.78473	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	2.0	0.06385	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.01277	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	2.0	0.06385	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.1277	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	2.0	91.3055	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.001277	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.01277	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	6.385E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	2.0	0.2554	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	2.0	0.006385	mg	

Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	2.0	0.06385	mg	
Material	2	Nickel Plate				2.0	1.59	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.0	0.00318	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	0.00159	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	2.0	1.58523	mg	
Material	2	Tin Plate				2.0	2.6	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.0	0.0052	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	2.0	2.59298	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	2.0	0.00182	mg	
Sub-Item	1	INSERT, COLD PRESS, PLTD				2.0	289.0182	mg	
Material	2	Tri Chrome Film				2.0	0.0182	mg	
Substance	3	Silicate(2-), hexafluoro-, hydrogen (1:2)	Supplier	16961-83-4	30.0	2.0	0.00546	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	10.0	2.0	0.00182	mg	
Substance	3	Chromium chloride (CrCl3), hydrate (1:6)	Supplier	10060-12-5	60.0	2.0	0.01092	mg	
Material	2	Zinc Alloy				2.0	289.0	mg	
Substance	3	Iron	Supplier	7439-89-6	0.08	2.0	0.2312	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.035	2.0	0.10115	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.0289	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	0.00289	mg	
Substance	3	Tin	Supplier	7440-31-5	0.0020	2.0	0.00578	mg	
Substance	3	Magnesium	Supplier	7439-95-4	0.05	2.0	0.1445	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.02	2.0	0.0578	mg	
Substance	3	Copper	Supplier	7440-50-8	0.1	2.0	0.289	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.289	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	2.0	0.1445	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.0289	mg	
Substance	3	Zinc	Supplier	7440-66-6	95.2145	2.0	275.1699	mg	
Substance	3	Aluminum	Supplier	7429-90-5	4.3	2.0	12.427	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.02	2.0	0.0578	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0030	2.0	0.00867	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	0.001445	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0040	2.0	0.01156	mg	
Sub-Item	1	SHELL, SZ3 RCPT 318 PLST				1.0	3087.779	mg	
Material	2	Tin Plate				1.0	51.989	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	0.0363923	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.10398	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	51.84863	mg	
Material	2	Copper Plate				1.0	31.79	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.03179	mg	
Substance	3	Copper	Supplier	7440-50-8	99.9	1.0	31.75821	mg	
Material	2	Carbon Steel				1.0	3004.0	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.08	1.0	2.4032	mg	
Substance	3	Sulfur	Supplier	7704-34-9	0.02	1.0	0.6008	mg	
Substance	3	Carbon	Supplier	7440-44-0	0.02	1.0	0.6008	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.3004	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.02	1.0	0.6008	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.15	1.0	4.506	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	3.004	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.3004	mg	
Substance	3	Molybdenum	Supplier	7439-98-7	0.75	1.0	22.53	mg	

Substance	3	Manganese	Supplier	7439-96-5	0.4	1.0	12.016	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.1	1.0	3.004	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.03004	mg	
Substance	3	Iron	Supplier	7439-89-6	98.1785	1.0	2949.28214	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.05	1.0	1.502	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.3004	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.01502	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	3.004	mg	