



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Benfer David W	<b>Contact Title</b>	Product Compliance Engineer for DND		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2018-04-04	<b>Contact Email</b>	dave.benfer@te.com				
<b>Contact Phone Number</b>	717-986-3725								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	5650861-5	<b>Amount</b>	9252.1176	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	ASSEMBLY,RE CEPTACLE,EUR OCARD,T	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-0117</b>	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
<b>Complex Article Description</b>	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	CONTACT,RE CEPT,VERT,E UROCARD,SO LDER,LEAD				64.0	49.5034	mg	
Material	2	Tin Plate				64.0	0.2593	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	64.0	5.186E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	64.0	0.2586	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	64.0	1.8151E-4	mg	
Material	2	Phos Bronze				64.0	48.49	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	64.0	45.9193	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	64.0	0.009698	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	64.0	0.004849	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	64.0	2.18205	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	64.0	0.0024245	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	64.0	0.04849	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	64.0	0.004849	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	64.0	4.849E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	64.0	0.14547	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	64.0	0.04849	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	64.0	0.04849	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	64.0	0.0024245	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	64.0	0.024245	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	64.0	0.04849	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	64.0	2.4245E-4	mg	
Material	2	Gold Plate				64.0	0.0146	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	64.0	0.0145562	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	64.0	4.38E-5	mg	

Material	2	Palladium-Nickel Plate				64.0	0.0092	mg	
Substance	3	Palladium	Supplier	7440-05-3	80.0	64.0	0.00736	mg	
Substance	3	Nickel	Nickel	7440-02-0	20.0	64.0	0.00184	mg	
Material	2	Nickel Plate				64.0	0.7303	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	64.0	0.0014606	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	64.0	7.303E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	64.0	0.72811	mg	
Sub-Item	1	EUROCARD 64 POS TTR B HSG				1.0	6083.9	mg	
Material	2	PBT-GF20-FR(17)				1.0	6083.9	mg	
Substance	3	C.I. Pigment Yellow 119	Supplier	68187-51-9	1.0	1.0	60.839	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	18.0	1.0	1095.102	mg	
Substance	3	C.I. Disperse Yellow 201	Supplier	80748-21-6	0.0020	1.0	0.12168	mg	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	1.0	12.1678	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	1.0	1.0	60.839	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.5	1.0	30.4195	mg	
Substance	3	Carbon black	Supplier	1333-86-4	0.1	1.0	6.0839	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	48.498	1.0	2950.56982	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	1520.975	mg	
Substance	3	Zinc sulfide (ZnS)	Supplier	1314-98-3	5.0	1.0	304.195	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	0.5	1.0	30.4195	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.2	1.0	12.1678	mg	