



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	TE Product Compliance	Contact Title			
Company Unique ID	TE Connectivity	Response Date	2018-08-09	Contact Email	productcompliance@te.com				
Contact Phone Number	+001-800-522-6752								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	640583-1	Amount	4.18518	Version	-	Identity			
Manufacturer Item Name	06P UMNL HDR ASSY R/A 94VO	Weight Uom	g	Mfr Site		Authority			
Date		UOM	Each						
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	UMNL HDR PIN R/A PTPPHBZ				6.0	0.19803	g	
Material	2	Phos Bronze				6.0	0.1978	g	
Substance	3	Copper	Supplier	7440-50-8	94.6985	6.0	0.18731363	g	
Substance	3	Manganese	Supplier	7439-96-5	0.02	6.0	3.956E-5	g	
Substance	3	Chromium	Supplier	7440-47-3	0.01	6.0	1.978E-5	g	
Substance	3	Tin	Supplier	7440-31-5	4.5	6.0	0.008901	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	6.0	9.89E-6	g	
Substance	3	Iron	Supplier	7439-89-6	0.1	6.0	1.978E-4	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	6.0	1.978E-5	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	6.0	1.978E-6	g	
Substance	3	Zinc	Supplier	7440-66-6	0.3	6.0	5.934E-4	g	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	6.0	1.978E-4	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	6.0	1.978E-4	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	6.0	9.89E-6	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	6.0	9.89E-5	g	
Substance	3	Nickel	Nickel	7440-02-0	0.1	6.0	1.978E-4	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	6.0	9.89E-7	g	
Material	2	Tin Plate				6.0	2.3E-4	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	6.0	4.6E-7	g	
Substance	3	Tin	Supplier	7440-31-5	99.73	6.0	2.2938E-4	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	6.0	1.61E-7	g	
Sub-Item	1	06P UMNL HDR HSG PC R/A				1.0	2.997	g	
Material	2	PA				1.0	2.997	g	
Substance	3	Water	Supplier	7732-18-5	0.3262	1.0	0.00977621	g	
Substance	3	2H-Azepin-2-one, hexahydro-	Supplier	105-60-2	0.4637	1.0	0.01389709	g	

Substance	3	Siloxanes and Silicones, di-Me	Supplier	63148-62-9	3.0E-4	1.0	8.991E-6	g	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	0.9451	1.0	0.02832465	g	
Substance	3	Benzenepropamide, N,N-1,6-hexanediylbis[3,5-bis(1,1-dimethylethyl)-4-hydroxy-	Supplier	23128-74-7	0.4004	1.0	0.01199999	g	
Substance	3	1,2-Ethanediamine	Supplier	107-15-3	0.0033	1.0	9.8901E-5	g	
Substance	3	Phosphoric acid, sodium salt, hydrate (1:2:12)	Supplier	10039-32-4	0.025	1.0	7.4925E-4	g	
Substance	3	Octadecanoic acid, calcium salt (2:1)	Supplier	1592-23-0	0.2012	1.0	0.00602996	g	
Substance	3	Octadecanamide, N,N-1,2-ethanediylbis-	Supplier	110-30-5	0.1901	1.0	0.0056973	g	
Substance	3	1,3,5-Triazine-2,4,6-(1H,3H,5H)-trione, compd. with 1,3,5-triazine-2,4,6-triamine (1:1)	Supplier	37640-57-6	9.0717	1.0	0.27187885	g	
Substance	3	Hexanedioic acid, polymer with hexahydro-2H-azepin-2-one and 1,6-hexanediamine	Supplier	24993-04-2	88.373	1.0	2.64853881	g	