



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Wu, Cc	<b>Contact Title</b>	Engineer Product Compliance china		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2018-06-12	<b>Contact Email</b>	cc.wu@te.com				
<b>Contact Phone Number</b>	86-2124071672								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	640250-6	<b>Amount</b>	1642.63	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	06P SL156 HSG W/LCK RAMP NATL	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-0117</b>	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	Nylon Compound				1.0	1642.63	mg	
Material	2	PA				1.0	1642.63	mg	
Substance	3	Water	Supplier	7732-18-5	0.3262	1.0	5.35826	mg	
Substance	3	2H-Azepin-2-one, hexahydro-	Supplier	105-60-2	0.4637	1.0	7.61688	mg	
Substance	3	Siloxanes and Silicones, di-Me	Supplier	63148-62-9	3.0E-4	1.0	0.00492789	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediy)imino-1,6-hexanediy]	Supplier	32131-17-2	0.9451	1.0	15.5245	mg	
Substance	3	Benzenepropanamide, N,N-1,6-hexanediybis[3,5-bis(1,1-dimethylethyl)-4-hydroxy-	Supplier	23128-74-7	0.4004	1.0	6.57709	mg	
Substance	3	1,2-Ethanediamine	Supplier	107-15-3	0.0033	1.0	0.05420679	mg	
Substance	3	Phosphoric acid, sodium salt, hydrate (1:2:12)	Supplier	10039-32-4	0.025	1.0	0.41066	mg	
Substance	3	Octadecanoic acid, calcium salt (2:1)	Supplier	1592-23-0	0.2012	1.0	3.30497	mg	
Substance	3	Octadecanamide, N,N-1,2-ethanediybis-	Supplier	110-30-5	0.1901	1.0	3.12264	mg	
Substance	3	1,3,5-Triazine-2,4,6-(1H,3H,5H)-trione, compd. with 1,3,5-triazine-2,4,6-triamine (1:1)	Supplier	37640-57-6	9.0717	1.0	149.01447	mg	
Substance	3	Hexanedioic acid, polymer with hexahydro-2H-azepin-2-one and 1,6-hexanediamine	Supplier	24993-04-2	88.373	1.0	1451.64141	mg	