



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer David W	Contact Title	Product Compliance Engineer for DND		
Company Unique ID	TE Connectivity	Response Date	2017-08-31	Contact Email	dave.benfer@te.com				
Contact Phone Number	1-717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	7-1734857-5	Amount	7393.62	Version	-	Identity			
Manufacturer Item Name	PCI EXP STRADDLE 98P BLK 30u"	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Material	1	Tin Plating				1.0	5.3	mg	
Substance	2	Tin	Supplier	7440-31-5	99.9	1.0	5.2947	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.1	1.0	0.0053	mg	
Material	1	Au Plating				1.0	2.02	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.1	1.0	0.00202	mg	
Substance	2	Gold	Supplier	7440-57-5	99.9	1.0	2.01798	mg	
Material	1	POLYESTER Compound - Black				1.0	4238.0	mg	
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	33.0	1.0	1398.54	mg	
Substance	2	Benzene, ethenyl-, homopolymer, brominated	Supplier	88497-56-7	22.0	1.0	932.36	mg	
Substance	2	1,4-Benzenedicarb oxylic acid, polymer with 2-methyl-1,8-octanediamine and 1,9-nonanediamine	Supplier	169284-22-4	42.0	1.0	1779.96	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	1.0	127.14	mg	
Material	1	Base Material-PHOSPHOR BRONZE				1.0	1257.0	mg	
Substance	2	Zinc	Supplier	7440-66-6	0.2	1.0	2.514	mg	
Substance	2	Tin	Supplier	7440-31-5	6.75	1.0	84.8475	mg	
Substance	2	Copper	Supplier	7440-50-8	92.55	1.0	1163.3535	mg	
Substance	2	Phosphorus	Supplier	7723-14-0	0.35	1.0	4.3995	mg	
Substance	2	Iron	Supplier	7439-89-6	0.1	1.0	1.257	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.6285	mg	

Material	1	LCP				1.0	1880.0	mg	
Substance	2	Talc (Mg ₃ H ₂ (SiO ₃) ₄)	Supplier	14807-96-6	20.0	1.0	376.0	mg	
Substance	2	1,3-Benzenedicarboxylic acid, polymer with 1,4-benzenedicarboxylic acid, [1,1-biphenyl]-4,4-diol and 4-hydroxybenzoic acid	Supplier	60088-52-0	55.0	1.0	1034.0	mg	
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	20.0	1.0	376.0	mg	
Substance	2	Carbon black	Supplier	1333-86-4	5.0	1.0	94.0	mg	
Material	1	Nickel Plating				1.0	11.3	mg	
Substance	2	Nickel	Nickel	7440-02-0	99.9	1.0	11.2887	mg	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.1	1.0	0.0113	mg	