



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Penica, John R	Contact Title	Sr Mgr Engineering		
Company Unique ID	TE Connectivity	Response Date	2017-08-08	Contact Email	jrpenica@te.com				
Contact Phone Number	+1-717-592-3266								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	8-1437657-8	Amount	26.6901	Version	-	Identity			
Manufacturer Item Name	8PCV-05-006=#8 TRIBARRIER	Weight Uom	g	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Material	1	Inulating body				1.0	11.02	g	
Substance	2	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	0.551	g	
Substance	2	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	1.0	1.0	0.1102	g	
Substance	2	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	3.306	g	
Substance	2	1,4-Benzenedicarboxylic acid, polymer with 1,4-butanediol	Supplier	26062-94-2	55.0	1.0	6.061	g	
Substance	2	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol], bis(2,4,6-tribromophenyl) ester	Brominated Flame Retardants (other than PBBs or PBDEs)	71342-77-3	9.0	1.0	0.9918	g	
Material	1	Brass_Termination				1.0	5.14	g	
Substance	2	Copper	Supplier	7440-50-8	68.0	1.0	3.4952	g	
Substance	2	Zinc	Supplier	7440-66-6	32.0	1.0	1.6448	g	
Material	1	Tin_Plating				1.0	5.0E-5	g	
Substance	2	Tin	Supplier	7440-31-5	100.0	1.0	5.0E-5	g	
Material	1	Screw				1.0	10.53	g	
Substance	2	Carbon	Supplier	7440-44-0	0.19	1.0	0.020007	g	
Substance	2	Silicon	Supplier	7440-21-3	0.0070	1.0	7.371E-4	g	
Substance	2	Aluminum	Supplier	7429-90-5	0.038	1.0	0.0040014	g	
Substance	2	Iron	Supplier	7439-89-6	98.89	1.0	10.413117	g	
Substance	2	Sulfur	Supplier	7704-34-9	0.013	1.0	0.0013689	g	
Substance	2	Manganese	Supplier	7439-96-5	0.85	1.0	0.089505	g	
Substance	2	Phosphorus	Supplier	7723-14-0	0.012	1.0	0.0012636	g	
Material	1	Zinc_Plating				1.0	5.0E-5	g	
Substance	2	Chromium	Supplier	7440-47-3	1.0	1.0	5.0E-7	g	
Substance	2	Zinc	Supplier	7440-66-6	99.0	1.0	4.95E-5	g	