



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Wu, Cc	Contact Title	Engineer Product Compliance china		
Company Unique ID	TE Connectivity	Response Date	2018-02-26	Contact Email	cc.wu@te.com				
Contact Phone Number	86-2124071672								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	640453-6	Amount	499.526	Version	-	Identity			
Manufacturer Item Name	06P MTA100 HDR ASSY SQ R/A	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	Brass Square				6.0	47.171	mg	
Material	2	Brass Wire				6.0	46.5	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	6.0	33.2475	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	6.0	4.65E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0226	6.0	13.03051	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	6.0	0.02325	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	6.0	4.65E-4	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	6.0	0.02325	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	6.0	0.0465	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0099	6.0	0.0046035	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	6.0	0.00465	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	6.0	0.02325	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	6.0	0.002325	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	6.0	2.325E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	6.0	0.093	mg	
Material	2	Tin Plate				6.0	0.477	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	6.0	9.54E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	6.0	0.47571	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	6.0	3.339E-4	mg	
Material	2	Nickel Plate				6.0	0.194	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	6.0	3.88E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	6.0	1.94E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	6.0	0.19342	mg	
Sub-Item	1	Polyester Compound				1.0	216.5	mg	
Material	2	PBT				1.0	216.5	mg	

Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	1.0	0.433	mg	
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	5.0	1.0	10.825	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.1	1.0	0.2165	mg	
Substance	3	Antimony oxide (Sb ₂ O ₃)	Supplier	1309-64-4	8.0	1.0	17.32	mg	
Substance	3	7-Oxabicyclo[4.1.0]heptane-3-carboxylic acid, 7-oxabicyclo[4.1.0]hept-3-ylmethyl ester	Supplier	2386-87-0	0.1	1.0	0.2165	mg	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	1.0	1.0825	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	0.1	1.0	0.2165	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.5	1.0	1.0825	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	156042-31-8	30.0	1.0	64.95	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	111211-39-3	5.0	1.0	10.825	mg	
Substance	3	Acetic acid ethenyl ester, polymer with ethene	Supplier	24937-78-8	2.0	1.0	4.33	mg	
Substance	3	Phosphorous acid, decyl diphenyl ester	Supplier	3287-06-7	0.1	1.0	0.2165	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	48.4	1.0	104.786	mg	