


standard soldering pad dimensions

The optimum soldering pad dimensions may differ depending on soldering conditions, however, the following land dimensions are generally recommended.

Type	Style	Dimensions millimeters				
		Component Size	A	B	C	D
WG73	1E	0.5 X 1.0	0.2	1.1	1.0	0.45
	1J	0.8 X 1.6	0.4	1.7	1.6	0.65
	2A	1.25 X 2.0	0.55	2.35	2.0	0.9
WK73	2B/2B15	1.6 X 3.2	0.7	2.3	3.2	0.8
	2H/2H2	2.5 X 5.0	1.0	35	5.0	1.25
WU73	2J	3.1 X 4.6	1.6	3.9	4.75	1.15
	3A/3A3	3.1 X 6.4	1.6	3.9	6.4	1.15
RK73 RS73 SG73 RN73R RN73H SR73 LT73 NT73 RF73 HV73 LP73 SDT73	1F	0.4 X 0.2	0.12	0.48	0.18	0.18
	1H	0.6 X 0.3	0.25	0.7	0.3	0.225
	1E	1.0 X 0.5	0.5	1.3	0.3	0.4
	1J	1.6 X 0.8	1.0	2.0	0.6	0.5
	2A	2.0 X 1.25	1.3	2.5	1.05	0.6
	2B	3.2 X 1.6	2.2	4.0	1.4	0.9
	2E	3.2 X 2.5	2.2	4.0	2.3	0.9
	2H	5.0 X 2.5	3.3	6.1	2.3	1.4
	3A/W3W/W3A2	6.4 X 3.2	4.6	8.0	3.0	1.7
	07, W07	5.0 X 2.5	2.3	7.0	2.6	2.35
	1, W1	6.3 X 3.1	3.4	8.0	3.0	2.3
	2-3	11.5 X 7.0	5.4	15.0	5.0	4.8
SLP	2H, 2HW	5.1 X 2.5	3.3	6.1	3.0	1.4
	3A, 3AW	6.35 X 3.2	4.1	7.55	3.7	1.725
SLN	2, 3, 5	11.5 X 7.0	5.0	15.0	6.0	5.0
CCP	2E	3.2 X 2.5	2.2	5.0	2.0	1.4
	2B	3.2 X 1.6	2.2	5.0	1.4	1.4
CCF	1N, 1F	6.0 X 2.5	3.0	7.2	2.8	2.1
LPC	4045	4.5 X 4.0	1.5	5.1	3.5	1.8
	4235	4.5 X 4.2	1.9	5.5	2.6	1.8
	4545	4.1 X 4.6	2.9	5.3	4.7	1.2
KQT	0402	1.0 X 0.5	0.46	1.18	0.66	0.36
KQ KQC	0603	1.6 X 1.0	0.64	1.92	1.02	0.64
	0805	2.0 X 1.5	0.76	2.8	1.78	1.02
	1008	2.5 X 2.2	1.27	3.31	2.54	1.02
CZB CZP MHL	1E	0.50 X 0.10	0.4	1.6	0.6	—
	1J	0.80 X 1.6	0.55	2.6	0.94	—
	2A	1.25 X 2.0	0.66	3.0	1.45	—
	2B	1.6 X 3.2	1.5	4.4	1.8	—
TF	10	1.0 X 0.5	0.5	1.3	0.3	0.4
	16	1.6 X 0.8	1.0	2.0	0.6	0.5

Flat Type Components



Type	Style	Dimensions millimeters				
		Component Size	A	B	C	D
TLR	1E	1.0 X 0.5	0.2	1.3	0.6	0.55
	2A	2.0 X 1.25	0.5	2.5	1.3	1.0
	2BW/2BP (0.5mΩ)	3.2 X 1.6	0.6	4.0	1.8	1.7
	2BN/2B/2BW/2BP (1mΩ, 1.5mΩ)	3.2 X 1.6	0.8	4.0	1.8	1.6
	2BN/2B/2BW/2BP (2mΩ-20mΩ)	3.2 X 1.6	1.4	4.0	1.8	1.3
	2H, 2HW (0.5mΩ, 1mΩ)	5.0 X 2.5	1.0	6.1	3.0	2.55
	2H, 2HW (2mΩ-6mΩ)	5.0 X 2.5	1.3	6.1	3.0	2.4
	2H, 2HW (7mΩ-10mΩ)	5.0 X 2.5	3.3	6.1	3.0	1.4
	3AW (0.5-0.82mΩ)	6.35 X 3.18	0.8	7.55	3.83	3.375
	3AW (1mΩ-4mΩ)	6.35 X 3.18	1.45	7.55	3.83	3.05
	3AW (5mΩ-8mΩ)	6.35 X 3.18	3.45	7.55	3.83	2.05
	3AW (9mΩ, 10mΩ)	6.35 X 3.18	4.40	7.55	3.83	1.575
TLRH	3AP (0.5-0.82mΩ)	6.35 X 3.18	0.80	7.55	3.83	3.375
	3AP (1mΩ)	6.35 X 3.18	1.45	7.55	3.83	3.05
	3AP (2mΩ)	6.35 X 3.18	1.05	7.55	3.83	3.25
	3AP (3mΩ-4mΩ)	6.35 X 3.18	1.45	7.55	3.83	3.05
	3AP (5mΩ-8mΩ)	6.35 X 3.18	3.45	7.55	3.83	2.05
	3AP (9mΩ-10mΩ)	6.35 X 3.18	4.40	7.55	3.83	1.575
2A	6.35 X 3.18	3.45	7.55	3.83	2.05	
	2A	2.0 X 1.25	0.5	2.5	1.3	1.0
	3AW	6.3 X 3.2	4.4	7.5	3.7	1.55
3AP	6.3 X 3.2	2.15	7.55	3.83	2.7	

Specifications given herein may be changed at any time without prior notice. Please confirm technical specifications before you order and/or use.


12/05/19

standard soldering pad dimensions (continued)

The optimum soldering pad dimensions may differ depending on soldering conditions, however, the following land dimensions are generally recommended.


Type	Style	Dimensions millimeters			
		Component Size	A	B	C
TLRZ	1E	1.0 X 0.5	0.5	1.3	0.6
	1J	1.6 X 0.8	0.5	2.0	0.9
	2A	2.0 X 1.25	0.5	2.5	1.45
	2B	3.2 X 1.6	2.2	3.8	1.8
UR73	2A	2.0 X 1.25	1.3	2.6	1.1
	2B	3.2 X 1.6	2.2	4.2	1.6
UR73D	1E	1.0 X 0.5	0.4	1.7	0.5
	1J	1.6 X 0.8	0.5	2.5	0.9
	2A	2.0 X 1.25	0.8	3.4	1.3
	2B	3.2 X 1.6	1.2	4.6	1.8
	2H (10mΩ-30mΩ)	5.0 X 2.5	1.8	6.1	2.6
	2H (33mΩ-100mΩ)	5.0 X 2.5	3.3	6.1	2.5
	3A (10mΩ-30mΩ)	6.3 X 3.1	2.3	8.0	3.3
	3A (33mΩ-100mΩ)	6.3 X 3.1	4.6	8.0	3.2
	2A	2.0 X 1.25	1.2	3.4	1.3
UR73V	2B	3.2 X 1.6	2.2	4.2	1.6
	2A (10m-18m)	2.0 X 3.1	0.6	3.4	1.3
UR73VD	2A (20m-36m)	2.0 X 3.1	0.8	3.4	1.3
	2B (10m-13m)	3.2 X 1.6	0.7	4.4	1.6
	2B (15m-16m)	3.2 X 1.6	0.9	4.4	1.6
	2B (18m-20m)	3.2 X 1.6	1.0	4.4	1.6
	2B (22m-27m)	3.2 X 1.6	1.2	4.4	1.6
	1H	0.6 X 0.3	0.25-0.35	0.65-0.95	0.25-0.35
NV73 NV73DL	1E	1.0 X 0.5	0.51	1.73	0.51
	1J	1.6 X 0.8	1.0	3.0	1.2
	2A	2.0 X 1.25	1.2	4.0	1.0
	2B	3.2 X 1.6	2.2	5.0	1.3
	2E	3.2 X 2.5	2.2	5.0	2.2
	2J	4.5 X 3.2	3.0	5.8	2.9
	2L	5.7 X 5.0	4.5	7.5	4.7
NV73DS	2L	6.1 X 5.1	4.5	7.5	4.7
PS	L	6.3 X 3.15	3.4	7	3.4
	J	10.0 X 5.2	5.6	11	6.2
					1.8

Flat Type Components




current sense resistor—PSG/PSF

Dimensions inches (mm)									
Type	A	B	C	D	E	F	G	H	I
PSG4 (2725)	.078 (2.0)	.370 (9.4)	.220 (5.6)	.146 (3.7)	.031 (0.8)	.031 (0.8)	.307 (7.8)	.035 (0.9)	.138 (3.5)
PSF4 (1216)	.024 (0.6)	.142 (3.6)	.116 (2.95)	.059 (1.5)	.020 (0.5)	.024 (0.6)	.142 (3.6)	.028 (0.7)	.059 (1.5)



current sense resistor—CSR

Dimensions inches (mm)									
Type	L	W	A	B	C	D	E	F	G
CSR1	.393 (10.0)	.236 (6.0)	.039 (1.0)	.078 (2.0)	.196 (5.0)	.062 (1.6)	.118 (3.0)	.078 (2.0)	.039 (1.0)
CSR2	.472 (12.0)	.314 (8.0)	.062 (1.6)	.125 (3.2)	.236 (6.0)	.086 (2.2)	.208 (5.3)	.090 (2.3)	.045 (1.15)




resistor arrays-CN

Type	Style	Dimensions						
		Component Size	A	B	C	D	E	F
L*	W							
CNN	2A	2.54	2.0	1.2	2.8	0.6	0.4	1.27
							—	—

* n = number of resistors


Chip Networks




integrated passive devices-SOIC, TSSOP, QSOP & SOT23

Chip Size	Dimensions inches (mm)					
	A	B	C	D	E	F
N08	.028 (0.7)	.050 (1.27)	.094 (2.4)	.098 (2.5)	.287 (7.3)	.150 (3.81)
N14	.028 (0.7)	.050 (1.27)	.094 (2.4)	.098 (2.5)	.287 (7.3)	.300 (7.62)
N16	.028 (0.7)	.050 (1.27)	.094 (2.4)	.098 (2.5)	.287 (7.3)	.350 (8.89)
Q16	.012 (0.3)	.025 (0.63)	.050 (1.27)	.180 (4.56)	.280 (7.1)	.175 (4.45)
Q20	.012 (0.3)	.025 (0.63)	.050 (1.27)	.180 (4.56)	.280 (7.1)	.225 (5.72)
Q24	.012 (0.3)	.025 (0.63)	.050 (1.27)	.180 (4.56)	.280 (7.1)	.275 (6.99)
SOT23	.035 (0.9)	.037 (0.95)	.055 (1.4)	.031 (0.8)	.141 (3.6)	—

SOIC, TSSOP, QSOP




SOT23




Surface mount components-RD41, RN41, RM41, MLT, CC

Type	Style	Dimensions millimeters				
		Component Size	A	B	C	D
RD41	2A	2.0 X 1.25	1.3	1.3	2.0	1.3
	2ES 12M	3.5 X 1.40	1.5	2.2	1.5	2.0
	2D	3.2 X 1.55	1.5	2.2	1.5	2.0
	2E 25	5.9 X 2.2	2.0	3.0	3.0	4.0
	2H	5.9 X 2.2	2.0	3.0	3.0	4.0



other chips—RCS, RCT, RCU, RCW

Type	Dimensions millimeters	
	A	B
RCS	4.1-4.3	1.4-1.6
RCT	2.9-3.1	1.05-1.25
RCU	2.5-2.7	0.6-0.8
RCW	4.1-4.3	1.4-1.6



power chip inductor—LPC

Type	Dimensions inches (mm)			
	A	B	C	D
LPC4045	.059 (1.5)	.201 (5.1)	.138 (3.5)	.071 (1.8)
LPC4235	.075 (1.9)	.217 (5.5)	.102 (2.6)	.071 (1.8)
LPC4545	.114 (2.9)	.209 (5.3)	.185 (4.7)	.047 (1.2)

