



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	TE Product Compliance	<b>Contact Title</b>			
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2018-10-04	<b>Contact Email</b>	productcompliance@te.com				
<b>Contact Phone Number</b>	+001-800-522-6752								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	640454-5	<b>Amount</b>	0.49068242	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	05P MTA100 HDR ASSY SQ STR POL	<b>Weight Uom</b>	g	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EURoHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-0117</b>	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
<b>Complex Article Description</b>	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	Brass Square				2.675	0.087171	g	
Material	2	Tin Plate				2.675	4.77E-4	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.675	9.54E-7	g	
Substance	3	Tin	Supplier	7440-31-5	99.73	2.675	4.7571E-4	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	2.675	3.339E-7	g	
Material	2	Brass Wire				2.675	0.0865	g	
Substance	3	Copper	Supplier	7440-50-8	71.5	2.675	0.0618475	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.675	8.65E-7	g	
Substance	3	Zinc	Supplier	7440-66-6	28.0226	2.675	0.02423955	g	
Substance	3	Manganese	Supplier	7439-96-5	0.05	2.675	4.325E-5	g	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	2.675	8.65E-7	g	
Substance	3	Iron	Supplier	7439-89-6	0.05	2.675	4.325E-5	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.675	8.65E-5	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.0099	2.675	8.5635E-6	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.675	8.65E-6	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	2.675	4.325E-5	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	2.675	4.325E-6	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.675	4.325E-7	g	
Substance	3	Nickel	Nickel	7440-02-0	0.2	2.675	1.73E-4	g	
Material	2	Nickel Plate				2.675	1.94E-4	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.675	3.88E-7	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.675	1.94E-7	g	
Substance	3	Nickel	Nickel	7440-02-0	99.7	2.675	1.9342E-4	g	
Sub-Item	1	Polyester Compound				1.0	0.2575	g	
Material	2	PBT				1.0	0.2575	g	

Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	1.0	5.15E-4	g	
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	5.0	1.0	0.012875	g	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.1	1.0	2.575E-4	g	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	8.0	1.0	0.0206	g	
Substance	3	7-Oxabicyclo[4.1.0]heptane-3-carboxylic acid, 7-oxabicyclo[4.1.0]hept-3-ylmethyl ester	Supplier	2386-87-0	0.1	1.0	2.575E-4	g	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	1.0	0.0012875	g	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	0.1	1.0	2.575E-4	g	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.5	1.0	0.0012875	g	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	156042-31-8	30.0	1.0	0.07725	g	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	111211-39-3	5.0	1.0	0.012875	g	
Substance	3	Acetic acid ethenyl ester, polymer with ethene	Supplier	24937-78-8	2.0	1.0	0.00515	g	
Substance	3	Phosphorous acid, decyl diphenyl ester	Supplier	3287-06-7	0.1	1.0	2.575E-4	g	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	48.4	1.0	0.12463	g	