



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer		
Company Unique ID	TE Connectivity	Response Date	2018-06-07	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	66505-9	Amount	151.2533393	Version	-	Identity			
Manufacturer Item Name	SOCKET CONTACT, 20 DF	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	20 DF SCKT CONT				1.0	151.2533393	mg	
Material	2	Nickel Plate				1.0	2.606	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.005212	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.002606	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	2.59818	mg	
Material	2	Gold Plate				1.0	0.0133393	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	0.01329928	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	1.0	4.00179E-5	mg	
Material	2	Gold Flash				1.0	2.034	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	1.0	0.006102	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	1.0	2.0279	mg	
Material	2	Phos Bronze				1.0	146.6	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	1.0	138.828	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.02932	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.01466	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	1.0	6.597	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	1.0	0.00733	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	0.1466	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.01466	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.001466	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	1.0	0.4398	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	1.0	0.1466	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.1466	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.00733	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.0733	mg	

Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	0.1466	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	7.33E-4	mg	