



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer David W	Contact Title	Product Compliance Engineer for DND		
Company Unique ID	TE Connectivity	Response Date	2018-04-25	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	796136-1	Amount	1105.16	Version	-	Identity			
Manufacturer Item Name	ASSY, SMT BATTERY CONN	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	POSITIVE CONTACT, SMT				1.0	72.86	mg	
Material	2	Phos Bronze				1.0	71.19	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	1.0	67.41586	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.014238	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.007119	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	1.0	3.20355	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	1.0	0.0035595	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	0.07119	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.007119	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	7.119E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	1.0	0.21357	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	1.0	0.07119	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.07119	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.0035595	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.035595	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	0.07119	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	3.5595E-4	mg	
Material	2	Tin Plate				1.0	1.67	mg	
Substance	3	Tin	Supplier	7440-31-5	97.85	1.0	1.6341	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.00334	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.35	1.0	0.005845	mg	
Substance	3	Copper	Supplier	7440-50-8	1.5	1.0	0.02505	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00167	mg	
Sub-Item	1	NEGATIVE CONTACT, SMT				1.0	57.3	mg	
Material	2	Phos Bronze				1.0	55.57	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6985	1.0	52.62396	mg	

Substance	3	Manganese	Supplier	7439-96-5	0.02	1.0	0.011114	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	1.0	0.005557	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	1.0	2.50065	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	1.0	0.0027785	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	1.0	0.05557	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.005557	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	5.557E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	1.0	0.16671	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	1.0	0.05557	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.05557	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.0027785	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.027785	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	1.0	0.05557	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	2.7785E-4	mg	
Material	2	Tin Plate				1.0	1.73	mg	
Substance	3	Tin	Supplier	7440-31-5	97.85	1.0	1.69281	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.00346	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.35	1.0	0.006055	mg	
Substance	3	Copper	Supplier	7440-50-8	1.5	1.0	0.02595	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00173	mg	
Sub-Item	1	TOP LOAD BATTERY HOUSING				1.0	975.0	mg	
Material	2	LCP				1.0	975.0	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	292.5	mg	
Substance	3	1,4-Benzenedicarboxylic acid, polymer with [1,1-biphenyl]-4,4-diol, 4-hydroxybenzoic acid, 6-hydroxy-2-naphthalenecarboxylic acid and N-(4-hydroxyphenyl)acetamide	Supplier	147310-94-9	69.7	1.0	679.575	mg	
Substance	3	Octadecanoic acid, 1,1-[2,2-bis[[[1-oxooctadecyl]oxy]methyl]-1,3-propanediyl] ester	Supplier	115-83-3	0.3	1.0	2.925	mg	