

 <small>ASSOCIATION CONNECTING ELECTRONICS INDUSTRIES®</small>		Material Composition Declaration <small>© Copyright 2005. IPC, Bannockburn, Illinois. All rights reserved under both international and Pan-American copyright conventions.</small>		<small>This document is a declaration of the substances within the manufacturer listed item. Note: if the item is an assembly with lower level parts, the declaration encompasses all lower level materials for which the manufacturer has engineering responsibility.</small> Adobe Reader version 7.0.5 is required to complete this declaration.					
1752-2 1.1		IPC Web Site for Information on IPC-1752 Standard http://www.ipc.org/IPC-175x			Form Type * Distribute		Declaration Class * Class 6 - RoHS Yes/No, Homogeneous Materials and Mfg Informat		
Supplier Information									
Company Name * Ecliptek Corporation		Company Unique ID		Unique ID Authority		Response Date * 2009-05-01		Response Document ID	
Contact Name * Tom Culhane		Title - Contact V.P. of Engineering		Phone - Contact * (714) 433-1200		Email - Contact * quality@ecliptek.com			
Authorized Representative * Tom Culhane		Title - Representative V.P. of Engineering		Phone - Representative * (714) 433-1200		Email - Representative * quality@ecliptek.com		Supplier Comments or URL for Additional Information http://www.ecliptek.com/	
	Requester Item Number	Mfr Item Number	Mfr Item Name	Effective Date	Version	Manufacturing Site	Weight *	UOM	Unit Type
		E3WC Series		2005-09-02		China	158	mg	Each
	Alternate Recommendation				Alternate Item Comments				
Manufacturing Process Information									
Terminal Plating / Grid Array Material Matte Tin (Sn) - with Nickel (Ni) barrier		Terminal Base Alloy Kovar		J-STD-020 MSL Rating 1		Peak Process Body Temperature 230 C		Max Time at Peak Temperature 10 seconds	
								Number of Reflow Cycles 3	
Comments Terminal Plating Thickness: Tin (3 to 5µm), Nickel (3 to 4µm). RoHS Definition Addition: Quantity limit of 0.1% by mass (1000ppm) in homogeneous material for Decabromodiphenylether (or Deca-BDE) and Perfluorooctane Sulfonate (PFOS).									

Save the fields in this form to a file		Export Data		Import fields from a file into this form		Import Data		Locked	
RoHS Material Composition Declaration								Declaration Type *	
RoHS Directive 2002/95/EC		RoHS Definition: Quantity limit of 0.1% by mass (1000 PPM) in homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material for Cadmium							
<p>Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2002/95/EC and implemented by the laws of the European Union member states) of the part identified on this form contains lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a "RoHS restricted substance") in excess of the applicable quantity limit identified above. If a homogeneous material within the part contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components.</p> <p>Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form.</p> <p>Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part, and those certifications are at least as comprehensive as the certification in this paragraph.</p> <p>If the Company and the Supplier enter into a written agreement with respect to the identified part, the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Supplier's Standard Terms and Conditions of Sale applicable to such part shall apply.</p>									
RoHS Declaration *		3 - Item(s) does not contain RoHS restricted substances per the definition above except for lead in solders and selected exemptions, if any						Supplier Acceptance *	
		Accepted							
Exemptions: If the declared item does not contain RoHS restricted substances per the definition above except for defined RoHS exemptions, then select the corresponding response in the RoHS Declaration above and choose all applicable exemptions.									
Exemption List Version		EL-2006/690/EC							
		7a. Lead in high melting temperature type solders (i.e. lead based solder alloys containing 85% by weight or more lead).							
Declaration Signature									
Instructions: Complete all of the required fields on all pages of this form. Select the "Accepted" on the Supplier Acceptance drop-down. This will display the signature area. Digitally sign the declaration (if required by the Requester) and click on Submit Form to have the form returned to the Requester.									
Supplier Digital Signature		Tom Culhane <small>Digitally signed by Tom Culhane DN: cn=Tom Culhane, o=Eclipse Corporation, ou, email=tculhane@eclipse.com, c=US Date: 2009.05.01 07:33:46 -0700</small>							

Homogeneous Material Composition Declaration for Electronic Products

SubItem Instructions: The presence of any JIG Level A or B substances must be declared. [1] indicate the subpart in which the substance is located, [2] provide a description of the homogeneous material [3], enter the weight of the homogeneous material.

Substance Instructions: [A] select the Level (JIG A, JIG B, Requester or Supplier) [B] select the substance category (JIG or Requester) or enter a value (Supplier). [C] select the substance (JIG) or enter the substance and CAS (Other). [D] select a RoHS exemption, if applicable [E] enter the weight of the substance or the PPM concentration [F] Optionally enter the positive (+) and negative (-) tolerance in percent (Note: percent tolerance values are expected to cover a 3 sigma range of distribution unless otherwise noted).

Line Functions: +I Inserts a New Item /SubItem +M Inserts a new Material +C Inserts a new Substance Category +S Inserts a new Substance - Deletes the element line

	Item/SubItem Name		Homogeneous Material	Weight	Unit of Measure		Level	Substance Category		Substance	CAS	Exempt	Weight	Unit of Measure	Tolerance		PPM
															-	+	
	Header		Cover		mg		Supplier	Copper		Copper	7440-50-8		84.3	mg	10	10	
			Cover		mg		B	Nickel (external applic		Nickel	7440-02-0		41	mg	10	10	
			Cover		mg		Supplier	Zinc		Zinc	7440-66-6		23.2	mg	10	10	
			Cover		mg		Supplier	Manganese		Manganese	7439-96-5		0.5	mg	10	10	
			Cover		mg		Supplier	Glass		Silicon Dioxide	14808-60-7		0.6	mg	10	10	
			Cover		mg		Supplier	Cobalt		Cobalt	14808-60-7		0.9	mg	10	10	
			Cover		mg		Supplier	Iron		Iron	7439-89-6		3.2	mg	10	10	
			Cover		mg		Supplier	Tin		Tin	7440-31-5		0.2	mg	10	10	
			Seal		mg		A	Lead/Lead Compound		Lead	7439-92-1	7a. Lead	0.2	mg	10	10	
			Seal		mg		Supplier	Tin		Tin	7440-31-5		0.2	mg	10	10	
	Crystal		Resonator		mg		Supplier	Quartz		Silicon Dioxide	14808-60-7		3.2	mg	10	10	
			Plating		mg		Supplier	Silver		Silver	7440-22-4		0.1	mg	10	10	
	Epoxy		Epoxy		mg		Supplier	Resin		Resin	86729-25-1		0.3	mg	10	10	
			Conductor		mg		Supplier	Silver		Silver	7440-22-4		0.1	mg	10	10	