



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Penica, John R	Contact Title	Sr Mgr Engineering, IND Central Eng																											
Company Unique ID	TE Connectivity	Response Date	2018-03-14	Contact Email	jrpenica@te.com																													
Contact Phone Number		+1-717-592-3266																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	9-215079-0	Amount	882.0	Version	-	Identity																												
Manufacturer Item Name	MICRO-MATCH FOB.20P	Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH																																	
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	MICRO-MATCH FOB.CNT				20.0	21.4	mg																										
Material	2	Nickel Plate				20.0	1.0	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	20.0	0.0020	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	20.0	0.0010	mg																										
Substance	3	Nickel	Nickel	7440-02-0	99.7	20.0	0.997	mg																										
Material	2	Phos Bronze				20.0	18.4	mg																										
Substance	3	Copper	Supplier	7440-50-8	94.6985	20.0	17.42452	mg																										
Substance	3	Manganese	Supplier	7439-96-5	0.02	20.0	0.00368	mg																										
Substance	3	Chromium	Supplier	7440-47-3	0.01	20.0	0.00184	mg																										
Substance	3	Tin	Supplier	7440-31-5	4.5	20.0	0.828	mg																										
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	20.0	9.2E-4	mg																										
Substance	3	Iron	Supplier	7439-89-6	0.1	20.0	0.0184	mg																										
Substance	3	Antimony	Supplier	7440-36-0	0.01	20.0	0.00184	mg																										
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	20.0	1.84E-4	mg																										
Substance	3	Zinc	Supplier	7440-66-6	0.3	20.0	0.0552	mg																										
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	20.0	0.0184	mg																										
Substance	3	Cobalt	Supplier	7440-48-4	0.1	20.0	0.0184	mg																										
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	20.0	9.2E-4	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	20.0	0.0092	mg																										
Substance	3	Nickel	Nickel	7440-02-0	0.1	20.0	0.0184	mg																										
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	20.0	9.2E-5	mg																										
Material	2	Tin Plate				20.0	2.0	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	20.0	0.0040	mg																										
Substance	3	Tin	Supplier	7440-31-5	99.73	20.0	1.9946	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	20.0	0.0014	mg																										

Sub-Item	1	MICRO-MATCH F HSG.L				1.0	454.0	mg	
Material	2	PBT-GF20-FR(17)				1.0	454.0	mg	
Substance	3	Lead oxide (lead monoxide)	Lead/Lead Compounds	1317-36-8	0.0020	1.0	0.00908	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.5	1.0	2.27	mg	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.1	1.0	0.454	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	113.5	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	17.0	1.0	77.18	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	1.0	13.62	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.2	1.0	0.908	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	0.5	1.0	2.27	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	46.896	1.0	212.90784	mg	
Substance	3	Zinc sulfide (ZnS)	Supplier	1314-98-3	1.0	1.0	4.54	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	22.7	mg	
Substance	3	Benzenesulfonic acid, 4,5-dichloro-2-[2-[4,5-dihydro-3-methyl-5-oxo-1-(3-sulphophenyl)-1H-pyrazol-4-yl]diazenyl]-, calcium salt (1:1)	Supplier	65212-77-3	0.8	1.0	3.632	mg	
Substance	3	Arsenic oxide (As2O3)	Arsenic oxide (As2O3)	1327-53-3	0.0020	1.0	0.00908	mg	